



STANDARD 200V SERIES

OUTPUT POWER-SPEED CHARACTERISTICS


— : 30-minute rating, 50%ED
 --- : Continuous rating




5/3HP 3.7/2.2kW




7.5/5HP 5.5/3.7kW




10/7.5HP 7.5/5.5kW




15/10HP 11/7.5kW




20/15HP 15/11kW




25/20HP 18.5/15kW



30/25HP 22/18.5kW



40/30HP 30/22kW




50/40HP 37/30kW


STANDARD 400V SERIES

OUTPUT POWER-SPEED CHARACTERISTICS


— : 30-minute rating, 50%ED
 — : Continuous rating




7.5/5HP 5.5/3.7kW




10/7.5HP 7.5/5.5kW




15/10HP 11/7.5kW




20/15HP 15/11kW




25/20HP 18.5/15kW




30/25HP 22/18.5kW



40/30HP 30/22kW



50/40HP 37/30kW




60/50HP 45/37kW


WINDING SELECTION 200V SERIES

OUTPUT POWER-SPEED CHARACTERISTICS


— : 30-minute rating, 50%ED
 — : Continuous rating




7.5/5HP 5.5/3.7kW




10/7.5HP 7.5/5.5kW




15/10HP 11/7.5kW




20/15HP 15/11kW



25/20HP 18.5/15kW



30/25HP 22/18.5kW



40/27HP 30/20kW

WINDING SELECTION 400V SERIES

OUTPUT POWER-SPEED CHARACTERISTICS

— : 30-minute rating, 50%ED
 — : Continuous rating

