

PD.E7N.01 - 06/01/2009

Rated Input Voltage	Bypass E7NV	Rated Output Current (Amps)	Nominal HP ⁽¹⁾	Physical Dimensions (in.)			Weight (lbs.) ⁽²⁾	Dimension Drawing Number
				H	W	D ⁽⁴⁾		
208V	D002	2.4	1/2	41.43	9.54	12.53	70	DD.E7N.203.01
	D003	3.5	3/4					
	D004	4.6	1					
	D007	7.5	2					
	D010	10.6	3					
	D016	17	5					
	D024	24	7.5					
	D030	31	10					
	D046	46.2	15	52.38	15.43	16.87	150	DD.E7N.255.01
D059	59.4	20	52.38	15.43	16.87	150	DD.E7N.255.01	
D074	74.8	25						
480V	B001	1.6	1/2	41.43	9.54	12.53	70	DD.E7N.203.01
			3/4					
	B002	2.1	1					
	B003	3.4	2					
	B004	4.8	3					
	B007	7.6	5					
	B011	11	7.5					
	B014	14	10					
	B021	21	15					
	B027	27	20					
	B034	34	25					
	B040	40	30	52.38	15.43	16.87	150	DD.E7N.255.01
	B052	52	40	52.38	15.43	16.87	150	DD.E7N.255.01
B065	65	50						

(1) Horsepower rating is based on standard NEMA B 4-pole motor design as represented in NEC Table 430.150 Full-Load Current, Three-Phase Alternating Current Motors

(2) Data represents the total approx. weight of the drive with all possible standard options, not shipping weight.