



V74X NEMA 4X

RATED INPUT	MODEL # CIMR-V7xx	AMPS	HP	WT LBS
230V	20P24	1.6	1/4	7.8
	20P44	3.0	1/2	8.0
	20P74	5.0	3/4 & 1	8.2
460V	40P24	1.2	1/2	8.4
	40P44	1.8	3/4	8.4
	40P74	3.4	1 & 2	8.7

xx denotes AA-ZZ

UNITS: inch
[mm]

FOR REFERENCE ONLY UNLESS PROPERLY ENDORSED.



DR BY RIP 7.9.02
APPVL SR
REV. JCM 2.3.03

S - 5504