



FRAME	CONSTRUCTION	A MAX.	B MAX.	C MAX.	D	E	2F	H	U MAX.	P MAX.	U	AA	AB MAX.	AG MAX.	AH	AJ	AK	BA	BB	BF	BS	KEY
S6C	ROLLED STEEL	6.50	4.00	14.98	3.50	2.44	3.00	.35	6.71	6.48	.625	-	5.56	10.61	2.06	5.875	4.500	2.75	.13	3/8-16	5.25	19x19x1.38
143TC	ROLLED STEEL	6.50	6.50	15.04	3.50	2.75	4.00	.35	6.71	6.48	.875	-	5.56	10.61	2.12	5.875	4.500	2.75	.13	3/8-16	4.93	19x19x1.38
143TC	CAST IRON	7.12	5.00	13.68	3.50	2.75	4.00	.38	7.45	7.98	.875	1.09	7.04	9.25	2.12	5.875	4.500	2.62	.13	3/8-16	2.81	19x19x1.38
145TC	ROLLED STEEL	6.50	6.50	16.04	3.50	2.75	5.00	.35	6.71	6.48	.875	-	5.56	11.61	2.12	5.875	4.500	2.75	.13	3/8-16	5.93	19x19x1.38
145TC	CAST IRON	7.12	6.00	14.68	3.50	2.75	5.00	.35	7.45	7.98	.875	1.09	7.04	10.25	2.12	5.875	4.500	2.62	.13	3/8-16	3.81	19x19x1.38
182TC	ALUMINUM	8.50	7.75	17.94	4.50	3.75	4.50	.44	9.38	9.78	1.125	1.09	7.82	13.00	2.62	7.250	8.500	3.50	.27	1/2-13	3.25	25x25x1.75
182TC	CAST IRON	8.88	5.50	16.12	4.50	3.75	4.50	.41	9.36	9.76	1.125	1.09	8.08	11.75	2.62	7.250	8.500	3.50	.27	1/2-13	2.25	25x25x1.75
184TC	ALUMINUM	8.50	7.75	19.94	4.50	3.75	5.50	.44	9.38	9.78	1.125	1.09	7.82	15.00	2.62	7.250	8.500	3.50	.27	1/2-13	4.25	25x25x1.75
184TC	CAST IRON	8.88	6.50	17.12	4.50	3.75	5.50	.41	9.36	9.76	1.125	1.09	8.08	12.75	2.62	7.250	8.500	3.50	.27	1/2-13	2.75	25x25x1.75
213TC	ALUMINUM	9.50	8.75	20.24	5.25	4.25	5.50	.44	10.62	10.78	1.375	1.34	7.50	14.81	3.12	7.250	8.500	4.25	.28	1/2-13	5.25	31x31x2.38
213TC	CAST IRON	10.38	8.50	20.56	5.25	4.25	5.50	.44	10.97	11.50	1.375	1.09	9.31	15.12	3.12	7.250	8.500	4.25	.27	1/2-13	3.50	31x31x2.38
215TC	ALUMINUM	9.50	11.75	23.24	5.25	4.25	7.00	.44	10.62	10.78	1.375	1.34	7.50	17.81	3.12	7.250	8.500	4.25	.28	1/2-13	9.25	31x31x2.38
215TC	CAST IRON	10.38	11.50	22.74	5.25	4.25	7.00	.44	10.97	11.50	1.375	1.09	9.31	17.31	3.12	7.250	8.500	4.25	.27	1/2-13	6.18	31x31x2.38
254TC	ALUMINUM	11.50	14.50	26.87	6.25	5.00	8.25	.56	11.62	10.78	1.625	1.75	8.10	20.81	3.75	7.250	8.500	4.75	.27	1/2-13	10.40	38x38x2.88
254TC	CAST IRON	12.12	12.00	25.12	6.25	5.00	8.25	.53	14.09	14.27	1.625	1.25	9.83	19.06	3.75	7.250	8.500	4.75	.27	1/2-13	4.12	38x38x2.88
256TC	ALUMINUM	11.50	16.25	26.87	6.25	5.00	10.00	.56	11.62	10.78	1.625	1.75	8.10	20.81	3.75	7.250	8.500	4.75	.27	1/2-13	10.40	38x38x2.88
256TC	CAST IRON	12.18	12.00	24.88	6.25	5.00	10.00	.56	14.09	14.27	1.625	1.25	11.88	18.82	3.75	7.250	8.500	4.75	.27	1/2-13	5.00	38x38x2.88
284TC	CAST IRON	13.00	13.00	27.25	7.00	5.50	9.50	.56	14.16	14.32	1.875	1.50	12.31	20.57	4.38	9.000	10.500	4.75	.27	1/2-13	5.50	50x50x3.25

APPROVAL for CONSTRUCTION

Type _____ Frame _____ Part No. _____ Spec. _____
 HP _____ RPM _____ Volts _____ Phase _____
 Certified for: _____
 Customer Order No. _____
 Yaskawa Order No. _____ By _____ Date _____