





SIDE VIEW



FRONT VIEW




BOTTOM VIEW



(4) 7/16 x 9/16 MOUNTING SLOT



CROHM LLC
Cincinnati, OH USA



DYNAMIC BRAKING RESISTOR

DWG NO.	...	OHMS	...
PART NO.	...	AMPS	...
SO. NO.	...	WATTS	...
DATA	...	MFG	...

ASSEMBLED IN USA

SALES@CROHM.COM (613) 921-9400



WIRE R1 & R2 TO
TERMINAL BLOCK USING
#10 HIGH TEMP WIRE

STEPS R1-R2

OHMS 6.0

WATTS 14,000

GENERAL NOTES:

- A. UNLESS OTHERWISE NOTED:
1. ALL DIMENSIONS ARE IN INCHES.



CROHM LLC
Cincinnati, OH USA
(613) 921-9400
sales@crohm.com



DYNAMIC BRAKING RESISTOR

TEXT			
DWG. NO.	C24N	REV.	0
DRAWN BY	RAO	CHECKED BY	.
		DATE	00/00/00
			SHEET 1 of 1
			SIZE A