




FRONT VIEW COVER REMOVED




FRONT VIEW



SIDE VIEW



TOP VIEW



GERMANY
CROHM LLC
Chardon, OH USA

DYNAMIC BRAKING RESISTOR

DWG NO. _____ OHMS _____
PART NO. _____ AMPS _____
SO. NO. _____ WATTS _____
DATA _____ MFG _____
ASSEMBLED IN USA

SALES@CROHM.COM (313) 921-9400



WIRE: 14 AWG TO TERMINAL
BLOCK LEADS TO HIGH TEMP
WIRE

TAP DATA
STEPS: _____ OHMS _____ WATTS
R1-R2 XXX XXX

GENERAL NOTES:

- A. UNLESS OTHERWISE NOTED:
1. ALL DIMENSIONS ARE IN INCHES.

THIS DRAWING IS THE PROPERTY OF CROHM LLC AND SHALL REMAIN THE PROPERTY OF CROHM LLC. IT IS TO BE USED FOR THE PURPOSES FOR WHICH IT WAS DESIGNED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN CONSENT OF CROHM LLC.

GERMANY CROHM LLC Chardon, OH USA sales@crohm.com			
DATE	REV	DATE	REV
01/01/12	0	01/01/12	1
DYNAMIC BRAKING RESISTOR			
DATE	REV	DATE	REV
01/01/12	0	01/01/12	1
RAO			
A			