

Technical Note

Terminal Block Kit Comparisons

Applicable Products:

CBK-U-MP2A*, CBK-U-MP2B*, SBK-U-VBA*



Product: CBK-U-MP2A*, CBK-U-MP2B*, SBK-U-VBA*	Doc#: TN.MCD.11
Title: Terminal Block Kit Comparisons	

About This Document



This document contains a summary of differences between the following terminal block kits:

CBK-U-MP2A-01 vs. CBK-U-MP2A-01(A)

CBK-U-MP2B-01 vs. CBK-U-MP2B-01(A)

SBK-U-VBA-01 vs. SBK-U-VBA-01(A)

In each of the three comparisons of the terminal block kits, the terminal blocks are the same, so the terminal blocks are not shown in the images.

Cable in kit: CBK-U-MP2A-01	Cable in kit: CBK-U-MP2A-01(A)
 <p><i>Terminal block side</i> <i>I/O device side</i></p> <p>Outer Diameter: 8.5 mm Bend Radius: TBD Terminal Block Connector: Overmolded PVC with thumb screws I/O Device Connector: Plastic shell with thumb screws</p>	 <p><i>Terminal block side</i> <i>I/O device side</i></p> <p>Outer Diameter: 8.1 mm Bend Radius: 81 mm Terminal Block Connector: Metal cover with captive screws I/O Device Connector: Plastic shell with thumb screws</p>





Product: CBK-U-MP2A*, CBK-U-MP2B*, SBK-U-VBA*

Doc#: TN.MCD.11

Title: Terminal Block Kit Comparisons

Cable in kit: CBK-U-MP2B-01



I/O device side

Terminal block side

Outer Diameter: 8.5 mm

Bend Radius: TBD

Terminal Block Connector: Overmolded PVC
with thumb screws

I/O Device Connector: Overmolded PVC
with thumb screws

Cable in kit: CBK-U-MP2B-01(A)



I/O device side

Terminal block side

Outer Diameter: 8.1 mm

Bend Radius: 81 mm

Terminal Block Connector: Metal cover
with captive screws

I/O Device Connector: Plastic cover
with jack screws





Product: CBK-U-MP2A*, CBK-U-MP2B*, SBK-U-VBA*

Doc#: TN.MCD.11

Title: Terminal Block Kit Comparisons

Cable in kit: SBK-U-VBA-01



I/O device side

Terminal block side

Outer Diameter: 6.5 mm


Bend Radius: TBD

Terminal Block Connector: Overmolded PVC with thumb screws

I/O Device Connector: Overmolded PVC with latches

Outer Jacket Color: Gray

Cable in kit: SBK-U-VBA-01(A)



I/O device side

Terminal block side



(no image for terminal block connector)



Beige



Gray

Outer Diameter: 6.4 mm

Bend Radius: 64 mm

Terminal Block Connector: Metal cover with jack screws

I/O Device Connector: Plastic cover with captive screws

Outer Jacket Color: Gray or Beige