





C/C: FP65□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)		COOLING FANS
		STANDARD	WITH EMC FILTER	
2075□□□	200 TO 240	41 (90.4)	41 (90.4)	2
2088□□□		41 (90.4)	41 (90.4)	2
2114□□□		44 (97.0)	44 (97.0)	2
4077□□□	380 TO 480	44 (97.0)	44 (97.0)	2
4096□□□		46 (101.7)	46 (101.7)	2

□ denotes A-Z

YASKAWA



UNITS MM [IN]


SCALE 1:12

DRWN.	J. MATTAS	3-28-22
CHKD.	J. PIOTROWSKI	3-30-22
TECH.	L. UDDIN	4-4-22
APRV.	J. CAIRO	4-21-22


TITLE
FP605 DIMENSION DRAWING
FRAME SIZE 4A
IP55/UL TYPE 12 ENCLOSURE
WITH MAIN SWITCH

SIZE	A	PAGE	1 OF 3
DWG.NO.	DD.FP605.FR4A.T12.SW		


REV
1



Minimum Installation Clearances



YASKAWA



UNITS MM [IN]

SCALE 1:8

DRWN.	J. MATTAS	3-28-22
CHKD.	J. PIOTROWSKI	3-30-22
TECH.	L. UDDIN	4-4-22
APRV.	J. CAIRO	4-21-22

TITLE
FP605 DIMENSION DRAWING
FRAME SIZE 4A
IP55/UL TYPE 12 ENCLOSURE
WITH MAIN SWITCH

SIZE A
PAGE 3 OF 3
DWG.NO.
DD.FP605.FR4A.T12.SW

REV
1