




(6) Mounting Holes for M6 [1/4"] Screws.  
See Detail A for top mounting hole dimensions.



**Detail A**  
Top mounting hole dimensions  
Scale 1:1




The dimensions shown are for an IP20 Type Drive that has been converted to a NEMA Type 1 Drive by adding the parts from Fuse Ready NEMA 1 Kit part number UUX002341

C/C: GA80□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
4060□□□	380 TO 480	19.0 (41.9)	2

□ denotes A-Z

1	CORRECT VERTICAL DIMS P1
0	INITIAL RELEASE




DRWN.	J. MATTAS	8-28-25
CHKD.	J. PIOTROWSKI	8-28-25
TECH.	L. UDDIN	8-28-25
APRV.	M. BAUMGARDNER	8-29-25



TITLE  
GA800 DIMENSION DRAWING  
FRAME SIZE 3.5  
FUSE READY  
NEMA TYPE 1 ENCLOSURE

SIZE	A	PAGE	1 OF 3
DWG.NO.	DD.GA80.FR3.5.N1.F		


REV  
1



**Detail A - Input Terminals (Scale 1:6)**



**Detail with Type 1 Protective Covers (Kit)**



C/C:	TERMINAL SYMBOL	WIRE RANGE AWG (mm <sup>2</sup> )	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
GA80□	R/L1, S/L2, T/L3	8 - 2 (10 - 35)	M6	4.4 (39)
4060□□	U/T1, V/T2, W/T3	8 - 2 (10 - 35)	M5	4.1 - 4.5 (36 - 40)
	-, +1	8 - 2 (10 - 35)	M5	4.1 - 4.5 (36 - 40)
	B1, B2	14 - 6 (2.5 - 16)	M4	1.5 - 1.7 (13.5 - 15)
	⊕	8 - 4 (10 - 25)	M6	5.4 - 6.0 (47.8 - 53.1)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

**YASKAWA**

UNITS MM [IN]  
SCALE ABOVE

DRWN. J. MATTAS 8-28-25  
CHKD. J. PIOTROWSKI 8-28-25  
TECH. L. UDDIN 8-28-25  
APRV. M. BAUMGARDNER 8-29-25


TITLE  
GA800 DIMENSION DRAWING  
FRAME SIZE 3.5  
FUSE READY  
NEMA TYPE 1 ENCLOSURE

SIZE A PAGE 2 OF 3  
DWG.NO. DD.GA80.FR3.5.N1.F

REV 1

1 CORRECT VERTICAL DIMS P1  
0 INITIAL RELEASE

Minimum Installation Clearances



Note:  
For alternate mounting configurations, consult manual.

8	
1	CORRECT VERTICAL DIMS P1
0	INITIAL RELEASE



 UNITS MM [IN] SCALE 1:8	DRWN. J. MATTAS	8-28-25
	CHKD. J. PIOTROWSKI	8-28-25
	TECH. L. UDDIN	8-28-25
	APRV. M. BAUMGARDNER	8-29-25

TITLE	GA800 DIMENSION DRAWING
	FRAME SIZE 3.5
	FUSE READY
	NEMA TYPE 1 ENCLOSURE

SIZE	A	PAGE	3 OF 3	REV	1
DWG.NO.	DD.GA80.FR3.5.N1.F				