







The dimensions shown are for an IP20 drive that has been converted to a UL Type 1 drive by adding the parts from UL Type 1 kit part number ZBAA-GA50V2-1

C/C: HV35□	INPUT VOLTAGE (VAC)	WEIGHT Kg (lb)	COOLING FANS
B006□□□	200 TO 240 1-PHASE	1.9 (4.3)	0

□ denotes A-Z

YASKAWA



UNITS MM [IN]

SCALE 1:3


DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 2.4A
UL TYPE 1 ENCLOSURE


SIZE A
PAGE 1 OF 3
DWG.NO.
DD.HV305.FR2.4A.T1

REV
0

FRONT VIEW




BOTTOM VIEW



C/C: HV35□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
B006□□□	L/L1, N/L2	14 - 10 (2.5 - 6)	M3	0.6 - 0.8 (5 - 7)
	U/T1, V/T2, W/T3	14 - 10 (2.5 - 6)	M3	0.6 - 0.8 (5 - 7)
	- , +1	14 - 10 (2.5 - 6)	M3	0.6 - 0.8 (5 - 7)
	B1, B2	14 - 10 (2.5 - 6)	M3	0.6 - 0.8 (5 - 7)
	Ⓢ	14 - 10 (2.5 - 6)	M4	1.2 - 1.5 (11 - 13)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA

UNITS MM [IN]

SCALE 1:2


DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 2.4A
UL TYPE 1 ENCLOSURE

SIZE	A	PAGE	2 OF 3
DWG.NO.	DD.HV305.FR2.4A.T1		


REV
0

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

YASKAWA



DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 2.4A
UL TYPE 1 ENCLOSURE

SIZE A
PAGE 3 OF 3
DWG.NO.
DD.HV305.FR2.4A.T1

REV
0