






FRONT VIEW

BOTTOM VIEW



C/C: HV35□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2070□□□ 2082□□□	R/L1, S/L2, T/L3	14 - 2/0 (2.5 - 70)	M6	5.5 (49)
	U/T1, V/T2, W/T3	14 - 2/0 (2.5 - 70)	M6	5.5 (49)
	-, +1, +2	14 - 2/0 (2.5 - 70)	M6	5.5 (49)
	B1, B2	14 - 6 (2.5 - 16)	M4	1.7 (15)
	⊕	6 - 4 (16 - 25)	M6	5.4 - 6.0 (47.8 - 53.1)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA

UNITS MM [IN]
SCALE 1:4


DRWN. J. MATTAS 9-23-22
CHKD. J. PIOTROWSKI 9-26-22
TECH. L. UDDIN 9-27-22
APRV. J. CAIRO 9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 7
UL TYPE 1 ENCLOSURE

SIZE A
PAGE 2 OF 3
DWG.NO.
DD.HV305.FR7.T1

REV
0

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

YASKAWA

UNITS MM [IN]
SCALE 1:5

DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING FRAME SIZE 7 UL TYPE 1 ENCLOSURE

SIZE A	PAGE 3 OF 3	REV 0
DWG.NO.	DD.HV305.FR7.T1	