






Section C-C


EMC FILTER SWITCHES

EMC SW1

EMC SW2



Detail A
Scale 1:2




Detail B
Scale 1:2

C/C: HV60□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2143□□□	R/L1, S/L2, T/L3	6 - 250 (16 - 120)	M8	15 (133)
2169□□□	U/T1, V/T2, W/T3	6 - 250 (16 - 120)	M8	15 (133)
4156□□□	-, +1	6 - 250 (16 - 120)	M8	15 (133)
	⊕	8 - 2/0 (10 - 70)	M8	9 - 11 (79.7 - 97.4)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]

SCALE 1:8


DRWN.	J. MATTAS	3-25-24
CHKD.	J. PIOTROWSKI	4-1-24
TECH.	L. UDDIN	7-3-24
APRV.	M. BAUMGARDNER	7-8-24

TITLE
HV600 DIMENSION DRAWING
FRAME SIZE 6
IP55/UL TYPE 12 ENCLOSURE

SIZE A PAGE 2 OF 3
DWG.NO.
DD.HV60.FR6.T12


REV
0

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

YASKAWA



UNITS MM [IN]

SCALE 1:10

DRWN.	J. MATTAS	3-25-24
CHKD.	J. PIOTROWSKI	4-1-24
TECH.	L. UDDIN	7-3-24
APRV.	M. BAUMGARDNER	7-8-24

TITLE
HV600 DIMENSION DRAWING
FRAME SIZE 6
IP55/UL TYPE 12 ENCLOSURE

SIZE A	PAGE 3 OF 3	REV 0
DWG.NO.	DD.HV60.FR6.T12	