






Terminal and Wiring Information for HV35□2056

FRONT VIEW

BOTTOM VIEW




C/C: HV35□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2056□□□	R/L1, S/L2, T/L3	8 - 2 (10 - 35)	M5	4.5 (40)
	U/T1, V/T2, W/T3	8 - 2 (10 - 35)	M5	4.5 (40)
	-, +1, +2	8 - 2 (10 - 35)	M5	4.5 (40)
	B1, B2	14 - 6 (2.5 - 16)	M4	1.7 (15)
	Ⓢ	8 - 4 (10 - 25)	M6	5.4 - 6.0 (48 - 53)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]

SCALE 1:3

DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 6
UL TYPE 1 ENCLOSURE



SIZE A PAGE 2 OF 4
DWG.NO.
DD.HV305.FR6.T1

REV
0

Terminal and Wiring Information for HV35□4031 and HV35□4038

FRONT VIEW

BOTTOM VIEW




C/C: HV35□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
4031□□□ 4038□□□	R/L1, S/L2, T/L3	14 - 6 (2.5 - 16)	M4	1.7 (15)
	U/T1, V/T2, W/T3	14 - 6 (2.5 - 16)	M4	1.7 (15)
	-, +1, +2	8 - 2 (10 - 35)	M5	4.5 (40)
	B1, B2	14 - 6 (2.5 - 16)	M4	1.7 (15)
	Ⓢ	10 - 6 (6 - 16)	M6	5.4 - 6.0 (48 - 53)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]

SCALE 1:3


DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 6
UL TYPE 1 ENCLOSURE

SIZE A
PAGE 3 OF 4
DWG.NO.
DD.HV305.FR6.T1

REV
0

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

YASKAWA

UNITS MM [IN]
SCALE 1:4

DRWN.	J. MATTAS	9-23-22
CHKD.	J. PIOTROWSKI	9-26-22
TECH.	L. UDDIN	9-27-22
APRV.	J. CAIRO	9-27-22

TITLE
HV305 DIMENSION DRAWING
FRAME SIZE 6
UL TYPE 1 ENCLOSURE

SIZE A	PAGE 4 OF 4	REV 0
DWG.NO. DD.HV305.FR6.T1		