




(4) Mounting Holes for M5 [#10] Screws. See Detail A for top mounting hole dimensions.

Center of Gravity
Note: Dimensions shown are measured from the bottom left mounting hole


Nameplate

Keypad



Top Type 1 Protective Cover

Note: Protective covers are factory installed to the top and bottom of the drive to meet UL Type 1 requirements. Remove these covers when operating the drive within a panel. Removing these covers results in an enclosure rating of IP20.

Cooling fan location




Detail A
Top mounting hole dimensions
Scale 1:1



C/C: WM65□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)		COOLING FANS
		STANDARD	WITH EMC FILTER	
2011□□□	200 TO 240	6.0 (13.2)	6.5 (14.3)	1
2017□□□		6.0 (13.2)	6.5 (14.3)	1
4005□□□	380 TO 480	6.0 (13.2)	7.0 (15.4)	0
4008□□□		7.0 (15.4)	7.5 (16.5)	0
4011□□□		6.5 (14.3)	7.0 (15.4)	1
4014□□□		6.5 (14.3)	7.0 (15.4)	1

□ denotes A-Z

YASKAWA



UNITS MM [IN]


SCALE 1:6

DRWN.	J. MATTAS	1-8-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-17-25
APRV.	M. BAUMGARDNER	7-24-25


TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 1
IP20/UL TYPE 1 ENCLOSURE

SIZE A
PAGE 1 OF 3
DWG.NO.
DD.WM605.FR1.T1

REV
0




Minimum Installation Clearances (Scale 1:5)




Note:
For alternate mounting configurations, consult manual.

Panel Cutout (Scale 1:4) For External Heatsink Mounting Configuration



Notes:
Exposed heatsink minimum clearance D = 110 [4.33].
Refer to external heatsink instructions document for additional details.

YASKAWA



UNITS MM [IN]
SCALE ABOVE

DRWN.	J. MATTAS	1-8-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-17-25
APRV.	M. BAUMGARDNER	7-24-25

TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 1
IP20/UL TYPE 1 ENCLOSURE

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.WM605.FR1.T1		

REV
0