





C/C: WM65□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2343□□□	200 TO 240	101 (222)	3
2396□□□		107 (235)	3
4361□□□	380 TO 480	107 (235)	2
4414□□□		113 (249)	3

YASKAWA





DRWN.	J. MATTAS	1-9-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-14-25
APRV.	M. BAUMGARDNER	7-22-25

TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 10
IP20/BACKSIDE TYPE 12 ENCLOSURE

SIZE	A	PAGE	1 OF 3
DWG.NO.	DD.WM605.FR10.FLNG		

REV
0




C/C: WM65□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2343□□□	R/L1, S/L2, T/L3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
2396□□□	U/T1, V/T2, W/T3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
4361□□□	-, +1	4/0 - 400 x 2P (120 - 205 x 2P)	M12	35 (310)
4414□□□	Ⓢ	1 - 350 (120 - 240)	M12	32 - 40 (283 - 354)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]


SCALE 1:10

DRWN.	J. MATTAS	1-9-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-14-25
APRV.	M. BAUMGARDNER	7-22-25

TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 10
IP20/BACKSIDE TYPE 12 ENCLOSURE

SIZE	A	PAGE	2 OF 3
DWG.NO.	DD.WM605.FR10.FLNG		

REV
0



8		YASKAWA		DRWN.	J. MATTAS	1-9-25	TITLE iQpump605 DIMENSION DRAWING FRAME SIZE 10 IP20/BACKSIDE TYPE 12 ENCLOSURE	SIZE	A	PAGE	3 OF 3	REV 0	
				CHKD.	J. PIOTROWSKI	1-23-25		DWG.NO. DD.WM605.FR10.FLNG					
				TECH.	L. UDDIN	7-14-25							
				SCALE	1:8	APRV.		M. BAUMGARDNER	7-22-25				