






C/C: WM65□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2343□□□	R/L1, S/L2, T/L3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
2396□□□	U/T1, V/T2, W/T3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
	-, +1	4/0 - 400 x 2P (120 - 205 x 2P)	M12	35 (310)
	⊕	1 - 350 (120 - 240)	M12	32 - 40 (283 - 354)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]

SCALE 1:10


DRWN.	J. MATTAS	1-8-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-11-25
APRV.	M. BAUMGARDNER	7-24-25

TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 10
IP20/UL TYPE 1 ENCLOSURE

SIZE A PAGE 2 OF 3
DWG.NO.
DD.WM605.FR10.T1


REV
0

Minimum Installation Clearances (Scale 1:10)



Note:
For alternate mounting configurations, consult manual.

YASKAWA



UNITS MM [IN]
SCALE ABOVE

DRWN.	J. MATTAS	1-8-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-11-25
APRV.	M. BAUMGARDNER	7-24-25

TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 10
IP20/UL TYPE 1 ENCLOSURE

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.WM605.FR10.T1		

REV
0