





(2)-Lifting Holes
Ø20 [Ø0.79]

Note: Spreader bar required to avoid damage during lifting

Nameplate

Center of Gravity
Note: Dimensions shown
are measured from the
bottom left mounting hole

Top Type 1 Protective Cover


Note: Protective covers are factory installed to the top and bottom of the drive to meet UL Type 1 requirements. Remove these covers when operating the drive within a panel. Removing these covers results in an enclosure rating of IP20. This note does not apply to model 4065. Do not remove the top cover from model 4065 when operating the drive within a panel.



Cooling fan location

The dimensions shown are for an IP20/Type 1 Drive that has been converted to a IP20/Backside Type 12 Drive by adding the parts from Type 12 heatsink external mounting kit number part number ZPSD-600-EH12-FR3

C/C: WM65□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)		COOLING FANS
		STANDARD	WITH EMC FILTER	
2046□□□	200 TO 240	14.6 (32.1)	15.6 (34.3)	1
2059□□□		15.6 (34.3)	16.6 (36.5)	1
4040□□□		15.6 (34.3)	16.6 (36.5)	1
4052□□□	380 TO 480	17.6 (48.7)	18.6 (40.9)	1
4065□□□		19.6 (43.1)	20.6 (45.3)	1

□ denotes A-Z






Section C-C

EMC FILTER SWITCHES


Note: EMC filter switches enabled only on models with built-in EMC filter

EMC SW1

EMC SW2



Detail A
Scale 1:2




Detail B
Scale 1:2

C/C: WM65□	TERMINAL SYMBOL	WIRE RANGE AWG (mm²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2046□□□	R/L1, S/L2, T/L3	8 - 2 (10 - 35)	M5	4.5 (40)
2059□□□	U/T1, V/T2, W/T3	8 - 2 (10 - 35)	M5	4.5 (40)
4040□□□	- , +1	8 - 2 (10 - 35)	M5	4.5 (40)
4052□□□ 4065□□□	Ⓢ	14 - 4 (2.5 - 25)	M6	4.0 - 5.0 (35 - 44)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]


SCALE 1:5

DRWN.	J. MATTAS	1-9-25
CHKD.	J. PIOTROWSKI	1-23-25
TECH.	L. UDDIN	7-15-25
APRV.	M. BAUMGARDNER	7-22-25

TITLE
iQpump605 DIMENSION DRAWING
FRAME SIZE 3
IP20/BACKSIDE TYPE 12 ENCLOSURE

SIZE A
PAGE 2 OF 3
DWG.NO.
DD.WM605.FR3.FLNG

REV
0



Notes:

Exposed heatsink minimum clearance D = 109 [4.29].
Refer to external heatsink instructions document for additional details.

8		YASKAWA		DRWN.	J. MATTAS	1-9-25	TITLE iQpump605 DIMENSION DRAWING FRAME SIZE 3 IP20/BACKSIDE TYPE 12 ENCLOSURE	SIZE	A	PAGE	3 OF 3	REV
				CHKD.	J. PIOTROWSKI	1-23-25		DWG.NO.				0
				TECH.	L. UDDIN	7-15-25		DD.WM605.FR3.FLNG				
				SCALE	1:6	APRV.		M. BAUMGARDNER	7-22-25			