





CONTROL TRANSFORMER PRIMARY CONNECTIONS			
INPUT VOLTS	TERMINALS		JUMPER LOCATION
	A	B	
460/480	(H1)	(H4)	(H2) TO (H3)

- NOTES:
- CUSTOMER TO CONNECT FIELD GROUND WIRING TO THE CABINET GROUND LUG.
 - CONDUIT FITTINGS/HUBS SHALL COMPLY WITH THE 'STANDARD FOR CONDUIT, TUBING, AND CABLE FITTINGS, UL 514B' OR CONDUIT FITTINGS HAVING THE SAME ENVIRONMENTAL RATING AS ENCLOSURE SHALL BE USED.
 - WITHOUT THE CIRCUIT BREAKER (OPTION PC, PE, OR PM), OR DISCONNECT SWITCH OPTION PD, THE DISCONNECT MEANS MUST BE SUPPLIED BY THE CUSTOMER.
 - BRANCH CIRCUIT PROTECTION TO BE SUPPLIED BY THE CUSTOMER WHEN NOTED ON THE CABINET DATA NAMEPLATE.
 - INSULATED TWISTED SHIELDED WIRE IS REQUIRED. SHIELD TO CONNECT TO PROPER TERMINALS AS SHOWN. CONNECT THE SHIELD ONLY AT THIS END. STUB AND ISOLATE THE OTHER END. DO NOT RUN THESE WIRES IN AC POWER AND AC CONTROL WIRES. KEEP ALL WIRING UNDER 50m IN LENGTH.
 - CUSTOMER TO ADJUST THE THERMOSTAT ON THE SPACE HEATER HR1 FOR THE MINIMUM DESIRED TEMPERATURE INSIDE THE DRIVE CABINET. THIS SET TEMPERATURE IS NORMALLY SELECTED TO BE SLIGHTLY HIGHER THAN THE MINIMUM AMBIENT TEMPERATURE OF THE AIR SURROUNDING THE CABINET, AND IS THE TEMPERATURE AT WHICH THE SPACE HEATER HR1 WILL SHUT OFF.
 - IF THIS CABINET IS WIRED TO A 3 PHASE, 4 WIRE WYE INPUT POWER TRANSFORMER, THEN ORDER NEUTRAL CURRENT TRANSFORMER:
 - FOR A 1000 AMP OR 1200 AMP CIRCUIT BREAKER (OPTION PC OR PE): PART NO. UPT000302.
 - FOR A 1600 AMP CIRCUIT BREAKER (OPTION PC OR PE): PART NO. UPT000303.
 - OPTIONS T3, TC, TD, TG, TH, OR TQ CONTROL (SEE UDE00583 FOR MORE INFORMATION).



- * - INDICATES COMPONENTS NOT SUPPLIED BY YASKAWA.
- - INDICATES CUSTOMER WIRING.
- - CONNECTED TO THE CABINET OR PANEL.

SEE DRAWING UDE00581 FOR CUSTOMER CONNECTION TABLES.
SEE DRAWING UDE00583 FOR DRIVE PARAMETER SETTINGS.

REVISIONS			
REV.	DESCRIPTION	ECO #	DRAWN BY
00	INITIAL RELEASE	-	J. ZAGORSKI

DATE	11/19/23
CHECKED	K. MALUSIC
DATE	11/28/23
APPROVED	R. JENSEN
DATE	12/11/23
ORIGINAL DESIGN	J. ZAGORSKI
DATE	11/19/23

TITLE	SCHEMATIC DIAGRAM GA800 CONFIGURED NORMAL DUTY - F2 ENCL TYPE 3R
SIZE	D
REVISION	00
PAGE	1 of 1
DRAWING #	DS.G8C3R.17