



101 FROM CUSTOMERS' 480VAC 3PH 60HZ AC LINES
 102
 103
 104
 105
 106
 107
 108
 109
 110
 111
 112
 113
 114
 115
 116
 117
 118
 119
 120
 121
 122
 123
 124
 125
 126
 127
 128
 129
 130
 131
 132
 133
 134
 135
 136
 137
 138
 139
 140
 141

A B C D E F G H J K

17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

* - INDICATES COMPONENTS NOT SUPPLIED BY YASKAWA.
 - - INDICATES CUSTOMER WIRING.
 SEE SHEET 2 FOR NOTES AND TABLES.

YASKAWA		DRAWN BY: P. STOCKUS		DATE: 11/27/13	TITLE: SCHEMATIC DIAGRAM	
CHECKED BY: D. TUMILSON		DATE: 12/2/13	REVISED BY: P. STOCKUS		DATE: 12/2/13	DESCRIPTION: IQPUMP1000 CONFIGURED 500HP 12-PULSE
REV.	DESCRIPTION	ECO #	DRAWN BY	DATE	REVISED BY	DESCRIPTION
04	REMOVED L2 REACTOR PER TEST RESULTS	5848	NSL	12/4/14	P. STOCKUS	1 of 2
03	CHANGED PM STYLE AND FAN SCHEMATIC	5448	NSL	8/11/14	P. STOCKUS	1 of 2
02	CHANGED TO JTD FUSES	5360	PS	6/9/14	P. STOCKUS	1 of 2

REV.	DESCRIPTION	ECO #	DRAWN BY	DATE
04	REMOVED L2 REACTOR PER TEST RESULTS	5848	NSL	12/4/14
03	CHANGED PM STYLE AND FAN SCHEMATIC	5448	NSL	8/11/14
02	CHANGED TO JTD FUSES	5360	PS	6/9/14

REV.	DESCRIPTION	ECO #	DRAWN BY	DATE
04	REMOVED L2 REACTOR PER TEST RESULTS	5848	NSL	12/4/14
03	CHANGED PM STYLE AND FAN SCHEMATIC	5448	NSL	8/11/14
02	CHANGED TO JTD FUSES	5360	PS	6/9/14

TABLE 1 FACTORY SET IQPUMP1000 CONFIGURED DRIVE PARAMETERS

PARAMETER	DATA	UNIT	DESCRIPTION/REMARKS
b1-01	SEE TABLE 2	N/A	AUTO SET-POINT SELECTION
b1-02	SEE TABLE 2	N/A	RUN COMMAND SELECTION
E1-01	480	VOLTS	STANDARD INPUT VOLTAGE SETTING
E1-05	460	VOLTS	STANDARD MAXIMUM OUTPUT VOLTAGE SETTING
E2-01	---	AMPS	MOTOR FULL LOAD CURRENT (TO BE SET BY USER)
H1-03	25	N/A	TERMINAL S3 = EXTERNAL FAULT (NORMALLY CLOSED)
H1-05	SEE TABLE 2	N/A	TERMINAL S5 FUNCTION SELECTION
H1-07	24	N/A	TERMINAL S7 = EXTERNAL FAULT (NORMALLY OPEN)
H1-27	5.00	SEC	TERMINAL S7 EXTERNAL FAULT (EF7) DELAY TIME
H3-02	SEE TABLE 2	N/A	TERMINAL A1 FUNCTION SELECTION
H3-06	SEE TABLE 2	N/A	TERMINAL A3 FUNCTION SELECTION
H3-09	SEE TABLE 2	N/A	TERMINAL A2 FEEDBACK SIGNAL LEVEL SELECTION
o2-03	1	N/A	USER INITIALIZATION FACTORY SET PARAMETER DEFAULT VALUES (FOUND IN A1-03="1110")
o3-02	1	N/A	COPY ALLOWED SELECTION ENABLED
P1-02	1 *	N/A	SYSTEM UNITS (WHERE 1 = POUNDS PER SQUARE INCH (PSI))
P1-03	00145 *	SYSTEM UNITS	FEEDBACK DEVICE SCALING (TO BE SET BY USER)
P5-01	SEE TABLE 2	N/A	HAND MODE FREQUENCY REFERENCE SELECTION
P5-02	---	HZ	HAND MODE FREQUENCY REFERENCE (TO BE SET BY USER) - SEE TABLE 2
P5-04	SEE TABLE 2	N/A	DRIVE KEYPAD HAND KEY ENABLE/DISABLE
Q1-01	----	SYSTEM UNITS	AUTO MODE SET-POINT REFERENCE (TO BE SET BY USER)

* = FACTORY 2-WIRE INITIALIZATION/DEFAULT SETTING

NOTES:

- CONNECTED TO THE CABINET. CUSTOMER TO CONNECT THE CABINET GROUND LUGS TO EARTH GROUND AND UTILITY GROUND.
- THE CUSTOMER MUST USE TYPE 3R RATED HUBS OR FITTINGS (OR EQUIVALENT) TO MAINTAIN THE ENCLOSURE RATING.
- N/A
- N/A
- INSULATED TWISTED SHIELDED WIRE IS REQUIRED. 2 OR 3 CONDUCTOR #18GA. (BELDEN NO. 8760 OR 8770, OR EQUIVALENT). SHIELD TO CONNECT TO PROPER TERMINAL AS SHOWN. CONNECT THE SHIELD ONLY AT THIS END. STUB AND ISOLATE THE OTHER END. DO NOT RUN THESE WIRES IN THE SAME CONDUIT AS THE AC POWER AND AC CONTROL WIRES.
- CUSTOMER TO ADJUST THE THERMOSTAT ON THE SPACE HEATER HR1 FOR THE MINIMUM DESIRED TEMPERATURE INSIDE THE DRIVE CABINET. THIS SET TEMPERATURE IS NORMALLY SELECTED TO BE SLIGHTLY HIGHER THAN THE MINIMUM AMBIENT TEMPERATURE OF THE AIR SURROUNDING THE CABINET, AND IS THE TEMPERATURE AT WHICH THE SPACE HEATER HR1 WILL SHUT OFF.
- SERIAL COMMUNICATIONS OPTIONS T2, TG, TH, TL, TO, OR TV (SEE TABLE 2):
 OPTION T2 = ETHERNET/IP; OPTION TG = DEVICENET; OPTION TH = PROFIBUS; OPTION TL = LONWORKS;
 OPTION TO = ETHERNET MODBUS TCP/IP AND OPTION TV = DRIVE EMBEDDED MODBUS PROTOCOL.
 THE DRIVE KEYPAD MUST BE IN "AUTO" MODE, IF SERIAL COMMUNICATIONS IS TO BE USED TO CONTROL THE DRIVE.
- WHEN OPTION TL IS ORDERED, A JUMPER IS REQUIRED FROM DRIVE TERMINALS (S1) TO (SN), SO THAT THE LONWORKS SERIAL COMMUNICATIONS CAN BE USED TO CONTROL THE DRIVE.
 CUSTOMER TO REPLACE THE JUMPER WITH NORMALLY CLOSED SAFETY INTERLOCKS, IF APPLICABLE.

* = FACTORY 2-WIRE INITIALIZATION/DEFAULT SETTING

FIELD WIRING PRESSURE WIRE CONNECTOR WIRE TYPE RANGE AND TIGHTENING TORQUE SPECIFICATIONS

FOR 0 TO 100 AMPS, USE 60-75°C COPPER WIRE AND ABOVE 100 AMPS, USE 75°C COPPER WIRE.

TABLE 2 FACTORY SET IQPUMP1000 CONFIGURED DRIVE PARAMETERS

CONTROL OPTION PRESENT	PARAMETER										SET-POINT		AUTO MODE			HAND MODE	
	b1-01	b1-02	H1-05	H3-02	H3-06	H3-09	P5-01	P5-04	DRIVE CONTROL BOARD SWITCH S1(A2)	DRIVE KEYPAD Q1-01	SERIAL COMM.	TERMINAL TBT1(4-6)	FEEDBACK SIGNAL	DRIVE KEYPAD IN THE "AUTO" MODE	DRIVE KEYPAD IN THE "HAND" MODE		
	0	0	8D	0	20	2	1	1	I *	YES	YES	YES	0-10 VDC	DRIVE KEYPAD IN THE "AUTO" MODE AND AUTO MODE RUN/STOP CONTACT	DRIVE KEYPAD IN THE "HAND" MODE		
NONE	0	0	8D	0	20	2	1	1	I *	YES	YES	YES	0-10 VDC	DRIVE KEYPAD IN THE "AUTO" MODE AND AUTO MODE RUN/STOP CONTACT	DRIVE KEYPAD IN THE "HAND" MODE		
NONE	0	0	8D	0	20	0	1	1	V	YES	YES	YES	0-10 VDC	DRIVE KEYPAD IN THE "AUTO" MODE AND AUTO MODE RUN/STOP CONTACT	DRIVE KEYPAD IN THE "HAND" MODE		
NONE	0	1	8D	0	20	2	1	1	I *	YES	YES	YES	0-10 VDC	DRIVE KEYPAD IN THE "AUTO" MODE AND AUTO MODE RUN/STOP CONTACT	DRIVE KEYPAD IN THE "HAND" MODE		
NONE	0	1	8D	0	20	0	1	1	V	YES	YES	YES	0-10 VDC	DRIVE KEYPAD IN THE "AUTO" MODE AND AUTO MODE RUN/STOP CONTACT	DRIVE KEYPAD IN THE "HAND" MODE		

* = FACTORY 2-WIRE INITIALIZATION/DEFAULT SETTING

CIRCUIT BREAKER (CB1)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)
AC MOTOR (A1-T1,T2,T3)	(1-3) x (3/0-500MCM)	(1-3) x 450
GROUND LUGS	CUSTOMER TO SUPPLY A UL LISTED CLOSED LOOP CONNECTOR PER AC DRIVE TECHNICAL MANUAL	275
NEUTRAL (TN1)	6 - 250MCM	275
CONTROL (TB1)	6 - 350MCM	275
	22 - 10	16 - 20



DRAWN BY: P. STOCKUS
 CHECKED: D. TUMILSON
 DATE: 11/27/13
 DATE: 12/2/13
 TITLE: SCHEMATIC DIAGRAM IQPUMP1000 CONFIGURED 500HP 12-PULSE
 THIS DOCUMENT AND INFORMATION CONTAINED HEREIN ARE CONFIDENTIAL AND SHOULD NOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA, INC.
 APPROVED BY: P. STOCKUS
 DATE: 12/2/13
 DRAWING # Q1C3J590-11
 SIZE D
 REVISION R04
 PAGE 2 of 2