



Product Service

CERTIFICATE

No. B 022021 0673 Rev. 02

Holder of Certificate: Yaskawa Electric Corp.
Tokyo Plant
480 Kamifujisawa, Iruma
Saitama 358-8555
JAPAN

Certification Mark:



Product: Electric Motors
AC Servo Motor

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 73561244-02

Valid until: 2029-10-03

Date, 2024-10-04

(Shigehisa Ishikawa)

CERTIFICATE

No. B 022021 0673 Rev. 02

Model(s): **SGMCS, SGM7E series**

Nomenclature for SGMCS Model:

Standard:

SGMCS - 02 B 3 A 1 1 -E
a b c d e f g h

- a. Motor type:
SGMCS Type
- b. Motor Torque:
- | | |
|----|---------|
| 02 | 2,0N·m |
| 05 | 5,0N·m |
| 07 | 7,0N·m |
| 04 | 4,0N·m |
| 10 | 10,0N·m |
| 14 | 14,0N·m |
| 08 | 8,0N·m |
| 17 | 17,0N·m |
| 25 | 25,0N·m |
| 16 | 16,0N·m |
| 35 | 35,0N·m |
- c. Motor Outer Diameter:
- | | |
|---|----------|
| B | 135 dia. |
| C | 175 dia. |
| D | 230 dia. |
| E | 290 dia. |
- d. Encoder:
- | | |
|---|-----------------------------|
| D | 20bit Serial Incremental |
| 3 | 20bit Serial Absolute Value |
- e. Design revision order:
- | | |
|---|---|
| A | Standard (Crossed roller bearing) |
| B | Standard (Angular contact ball bearing) |
| C | Standard (Angular contact ball bearing) |
- f. Connector Position:
- | | |
|---|------------------------|
| 1 | C-face |
| 2 | Flange mount type |
| 4 | C-face with cable type |
- g. Optional Specification:
Any number or alphabet numeral for non-critical optional provision
- h. Design of RoHS model:
- | | |
|-------|--------------------------|
| -E | RoHS Responses Model |
| blank | RoHS Non-responses Model |

CERTIFICATE

No. B 022021 0673 Rev. 02

Exclusive Design for Customer:

$\frac{\text{SGMCS}}{\text{a}}$ - $\frac{02}{\text{b}}$ $\frac{\text{B}}{\text{c}}$ $\frac{\text{D}}{\text{d}}$ $\frac{\text{A}}{\text{e}}$ - $\frac{*}{\text{f}}$ $\frac{*}{\text{g}}$ $\frac{*}{\text{h}}$ $\frac{*}{\text{i}}$

- a. Motor type:
SGMCS Type
- b. Motor Torque:
- | | |
|----|---------|
| 02 | 2,0N·m |
| 05 | 5,0N·m |
| 07 | 7,0N·m |
| 04 | 4,0N·m |
| 10 | 10,0N·m |
| 14 | 14,0N·m |
| 08 | 8,0N·m |
| 17 | 17,0N·m |
| 25 | 25,0N·m |
| 16 | 16,0N·m |
| 35 | 35,0N·m |
- c. Motor Outer Diameter:
- | | |
|---|----------|
| B | 135 dia. |
| C | 175 dia. |
| D | 230 dia. |
| E | 290 dia. |
- d. Encoder:
- | | |
|---|-----------------------------|
| D | 20bit Serial Incremental |
| 3 | 20bit Serial Absolute Value |
- e. Design revision order:
- | | |
|---|---|
| A | Standard (Crossed roller bearing) |
| B | Standard (Angular contact ball bearing) |
| C | Standard (Angular contact ball bearing) |
- f,g. Customer Code:
** Put any 2 digits alphanumeric
- h,i. Design revision order for customer:
** Put any 2 digits alphanumeric

Construction of exclusive design for customer

Type	Difference from the standard type	Drawing and parts list
SGMCS-10C3A-MB11	Cable direction and position only	DP0311394
SGMCS-17D3A-MB11	Cable direction and position only	DP0311398
SGMCS-35E3A-MB11	Cable direction and position only	DP0311400
SGMCS-08DDA-TE12	Type only (Customer code)	DP0310547 DP0311586 (Parts list, Table-2)
SGMCS-14C3B-NT21	Bearing cover size only	DP0350110
SGMCS-05B3B-NT11	Mechanical fixture is modified upon a client.	DP0312901
SGMCS-14C3B-NT12	Mechanical fixture is modified upon a client.	DP0312056
SGMCS-25D3B-NT11	Mechanical fixture is modified upon a client.	DP0312380
SGMCS-17D3B-MB21	Mechanical length, connector and cable.	DP0312422

CERTIFICATE

No. B 022021 0673 Rev. 02

Nomenclature for SGM7E Model:

Standard:

SGM7E - 02 B F A 1 1
a b c d e f g

- a. Motor type:
SGM7E type
- b. Motor Torque:
- | | |
|----|---------|
| 02 | 2,0N·m |
| 05 | 5,0N·m |
| 07 | 7,0N·m |
| 04 | 4,0N·m |
| 10 | 10,0N·m |
| 14 | 14,0N·m |
| 08 | 8,0N·m |
| 17 | 17,0N·m |
| 25 | 25,0N·m |
| 16 | 16,0N·m |
| 35 | 35,0N·m |
- c. Motor Outer Diameter:
- | | |
|---|----------|
| B | 135 dia. |
| C | 175 dia. |
| D | 230 dia. |
| E | 290 dia. |
- d. Encoder:
- | | |
|---|-----------------------------|
| F | 24bit Serial Incremental |
| 7 | 24bit Serial Absolute Value |
- e. Design revision order:
- | | |
|---|---|
| A | Standard (Angular contact ball bearing) |
| C | Manufactured in China (Angular contact ball bearing) |
| M | Manufactured in U.S.A. (Angular contact ball bearing) |
- f. Connector Position:
- | | |
|---|------------------------|
| 1 | C-face |
| 4 | C-face with cable type |
- g. Optional Specification:
- | | |
|---|----------------|
| 1 | Without option |
| 2 | High precision |

CERTIFICATE

No. B 022021 0673 Rev. 02

Exclusive Design for Customer:

SGM7E - 02 B F A - * * * *
a b c d e f g h i

- a. Motor type:
SGM7E Type
- b. Motor Torque:
 - 02 2,0N·m
 - 05 5,0N·m
 - 07 7,0N·m
 - 04 4,0N·m
 - 10 10,0N·m
 - 14 14,0N·m
 - 08 8,0N·m
 - 17 17,0N·m
 - 25 25,0N·m
 - 16 16,0N·m
 - 35 35,0N·m
- c. Motor Outer Diameter:
 - B 135 dia.
 - C 175 dia.
 - D 230 dia.
 - E 290 dia.
- d. Encoder:
 - F 24bit Serial Incremental
 - 7 24bit Serial Absolute Value
- e. Design revision order:
 - A Standard (Angular contact ball bearing)
 - C Manufactured in China (Angular contact ball bearing)
 - M Manufactured in U.S.A. (Angular contact ball bearing)
- f,g. Customer Code:
** Put any 2 digits alphanumeric
- h,i. Design revision order for customer:
** Put any 2 digits alphanumeric

INTERNATIONAL PROTECTION CLASS (IP class)

Motor type	IP Class
SGMCS	IP42
SGM7E	IP40

CERTIFICATE

No. B 022021 0673 Rev. 02

Electrical ratings –

SGMCS series

Model	Voltage / Phase	Amps(A)	Output(W)	Torque(N·m)
SGMCS-02Bxxxx	200 / 3	1,9	42	2,0
SGMCS-05Bxxxx	200 / 3	1,8	105	5,0
SGMCS-07Bxxxx	200 / 3	1,4	147	7,0
SGMCS-04Cxxxx	200 / 3	2,1	84	4,0
SGMCS-10Cxxxx	200 / 3	2,0	209	10,0
SGMCS-14Cxxxx	200 / 3	2,0	293	14,0
SGMCS-08Dxxxx	200 / 3	2,1	168	8,0
SGMCS-17Dxxxx	200 / 3	2,3	356	17,0
SGMCS-25Dxxxx	200 / 3	2,7	393	25,0
SGMCS-16ExAxx	200 / 3	3,5	335	16,0
SGMCS-35ExAxx	200 / 3	3,6	550	35,0
SGMCS-16ExBxx	200 / 3	3,3	335	16,0
SGMCS-35ExBxx	200 / 3	3,5	550	35,0
SGMCS-02BxCxx	200 / 3	1,8	42	2,0
SGMCS-05BxCxx	200 / 3	1,7	105	5,0
SGMCS-07BxCxx	200 / 3	1,4	147	7,0
SGMCS-04CxCxx	200 / 3	2,2	84	4,0
SGMCS-10CxCxx	200 / 3	2,2	209	10,0
SGMCS-14CxCxx	200 / 3	2,8	293	14,0
SGMCS-08DxCxx	200 / 3	1,9	168	8,0
SGMCS-17DxCxx	200 / 3	2,5	356	17,0
SGMCS-25DxCxx	200 / 3	2,6	393	25,0

SGM7E series

Model	Voltage / Phase	Amps(A)	Output(W)	Torque(N·m)
SGM7E-02Bxxxx	200 / 3	1,8	42	2,0
SGM7E-05Bxxxx	200 / 3	1,7	105	5,0
SGM7E-07Bxxxx	200 / 3	1,4	147	7,0
SGM7E-04Cxxxx	200 / 3	2,2	84	4,0
SGM7E-10Cxxxx	200 / 3	2,2	209	10,0
SGM7E-14Cxxxx	200 / 3	2,8	293	14,0
SGM7E-08Dxxxx	200 / 3	1,9	168	8,0
SGM7E-17Dxxxx	200 / 3	2,5	356	17,0
SGM7E-25Dxxxx	200 / 3	2,6	393	25,0
SGM7E-16Exxxx	200 / 3	3,3	335	16,0
SGM7E-35Exxxx	200 / 3	3,5	550	35,0

Parameters:

Rated voltage:	AC 200 V, 3phases
Rated input current:	1,4 - 3,6 A (SGMCS Model) 1,4 - 3,5 A (SGM7E Model)
Rated output power:	42 - 550 W (SGMCS, SGM7E Model)
Protection class:	I
Degree of protection:	IP42 (SGMCS Model) IP40 (SGM7E Model)

Remark:

When installing / inserting the equipment, all requirements of the mentioned test standard must be fulfilled.

Tested according to: EN 60034-1:2010
EN IEC 60034-5:2020