



RATED INPUT	MODEL GPD506V-	OUTPUT CURRENT RATING (AMPS)	DIMENSIONS IN INCHES															APPROX. WEIGHT (LBS.)
			MOUNTING		H	W	H2	W2	A	B	C	D	E	F	G	J	K	
			H1	W1														
208/ 230	A003	3.2	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	6.30	4.60	1.07	1.53	1.09	---	6.5
	A006	6	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	6.30	4.60	1.07	1.53	1.09	---	6.5
	A008	8	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	6.30	4.60	1.07	1.53	1.09	---	6.5
	A011	11	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	7.09	4.60	1.07	1.53	1.09	---	10
	A017	17.5	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	7.09	4.60	1.07	1.53	1.09	---	10
	A027	27	11.22	7.32	11.81	7.87	.31	.28	4.08	4.67	1/4	8.07	5.93	1.45	2.60	1.38	.88	12
	A036	36	11.22	7.32	11.81	7.87	.31	.28	4.08	4.67	1/4	8.07	5.93	1.45	2.60	1.38	.88	13
	A054	54	14.37	9.29	14.96	9.84	.30	.28	5.35	5.78	1/4	8.86	6.93	2.01	3.15	1.73	.88	24
A068	68	14.37	9.29	15.75	9.84	1.08	.28	5.35	5.78	1/4	8.86	6.93	2.01	3.15	1.73	.88	24	
460	B001	1.8	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	6.30	4.60	1.07	1.53	1.09	---	6.5
	B003	3.4	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	6.30	4.60	1.07	1.53	1.09	---	8.8
	B004	4.8	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	7.09	4.60	1.07	1.53	1.09	---	10
	B008	8	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	7.09	4.60	1.07	1.53	1.09	---	10
	B011	11	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	7.09	4.60	1.07	1.53	1.09	---	10
	B014	14	11.22	7.32	11.81	7.87	.31	.28	4.08	4.67	1/4	8.07	5.93	1.45	2.60	1.38	.88	13
	B021	21	11.22	7.32	11.81	7.87	.31	.28	4.08	4.67	1/4	8.07	5.93	1.45	2.60	1.38	.88	13
	B027	27	14.37	9.29	14.96	9.84	.30	.28	5.35	5.78	1/4	8.86	6.93	2.01	3.15	1.73	.88	24
B034	34	14.37	9.29	14.96	9.84	.30	.28	5.35	5.78	1/4	8.86	6.93	2.01	3.15	1.73	.88	24	
600	MODEL CIMR-P5M																	
	51P51F	3.9	10.47	4.96	11.02	5.51	.28	.28	---	3.24	#10	7.09	4.60	1.07	1.53	1.09	---	9
	53P51F	7	11.22	7.32	11.81	7.87	.31	.28	4.08	4.67	1/4	8.07	5.93	1.45	2.60	1.38	.88	13
	55P51F	11	11.22	7.32	11.81	7.87	.31	.28	4.08	4.67	1/4	8.07	5.93	1.45	2.60	1.38	.88	14
	50111F	19	14.37	9.29	14.96	9.84	.30	.28	5.35	5.78	1/4	8.86	6.93	2.01	3.15	1.73	.88	29
	50151F	25	14.37	9.29	14.96	9.84	.30	.28	5.35	5.78	1/4	8.86	6.93	2.01	3.15	1.73	.88	29

FOR REFERENCE ONLY UNLESS PROPERLY ENDORSED.



DR BY RIP 2.22.01
APPVL. SR 2-01