


DIMENSIONS: E7 (NEMA 1)

208/240V (88-115AMPS) 480V (67.2-125AMPS)

S - 5517



RATED INPUT	MODEL CIMR-E7U	OUTPUT CURRENT RATING (AMPS)	NOM. HP	DIMENSIONS IN INCHES																	APPROX. WEIGHT (LBS.)
				MOUNTING		H	W	H2	W2	D	D1	A	B	C	E	F	G	J	K	L	
				H1	W1																
208V	20221	88	30	15.16	7.88	21.06	10.00	.30	1.16	10.24	3.94	1/4	5.00	6.50	7.88	1.73	5.90	2.44	1.97	1.10	53
	20301	115	40	17.13	8.86	24.21	10.98	.30	1.16	10.24	3.94	1/4	5.00	6.50	7.88	1.73	5.90	2.44	1.97	1.10	80
240V	20221	88	30	15.16	7.88	21.06	10.00	.30	1.16	10.24	3.94	1/4	5.00	6.50	7.88	1.73	5.90	2.44	1.97	1.10	53
	20301	115	40	17.13	8.86	24.21	10.98	.30	1.16	10.24	3.94	1/4	5.00	6.50	7.88	1.73	5.90	2.44	1.97	1.10	80
480V	40301	87.2	40-50	17.13	8.86	21.06	10.98	.30	1.16	10.24	3.94	1/4	5.00	6.50	7.88	1.73	5.90	1.97	1.97	1.10	53
	40371	77	60	21.06	10.24	25.00	12.95	.30	1.36	11.22	4.13	1/4	5.18	6.70	8.07	1.73	6.70	1.97	1.97	1.10	88
	40451	96	75	21.06	10.24	28.15	12.95	.30	1.36	11.22	4.13	1/4	5.18	6.70	8.07	1.73	6.70	2.44	1.97	1.10	88
	40551	125	100	21.06	10.24	28.15	12.95	.30	1.36	11.22	4.13	1/4	5.18	6.70	8.07	1.73	6.70	2.44	1.97	1.10	88

FOR REFERENCE ONLY UNLESS PROPERLY ENDORSED.
 IN ORDER TO ACHIEVE ADEQUATE COOLING
 THE DRIVE MUST BE POSITIONED TO ALLOW A MINIMUM
 OF FREE AIR SPACE OF 1.2 INCHES ON SIDES AND
 5 INCHES TOP AND BOTTOM