

CUSTOMER WIRING REQUIREMENTS												
• FOR 0 TO 100 AMPS, USE A MINIMUM OF 60° - 75° C COPPER WIRE. (USE COPPER CONDUCTORS ONLY)												
• FOR ABOVE 100 AMPS, USE A MINIMUM OF 75° C COPPER WIRE. (USE COPPER CONDUCTORS ONLY)												

TABLE 1			A.C. LINE WIRING				CONTROL WIRING											
IQPUMP605 CONFIGURED MODEL NO. BASE NUMBER Q6C2XXXX			WITH OPTION PC, PE CIRCUIT BREAKER CB1				A1 TERMINAL BLOCKS TB1,TB3-TB7		A1 TERMINAL BLOCK TB2 (FE)		PANEL TERMINAL BLOCK TB1,TB4							
208V	240V	480V	MFG. PART NUMBER	CURRENT RATING (AMPS)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)						
D004	A004	B002	H_ _36015	15	14 - 10 OR 8 - 3/0	50 OR 120	24 - 16	4.4 - 5.3	24 - 18	8.9 - 10.7	26 - 10	5.3 - 7.1						
D007	A006	B003																
D010	A009	B004																
		B007																
		B011																
D016	A015	B014	H_ _36020	20														
	A022	B021	H_ _36025	25														
D024		B027	H_ _36030	30														
	A028		H_ _36035	35														
D030		B034	H_ _36040	40														
	A042	B040	H_ _36050	50														
D046		B052	H_ _36060	60														
D059	A054		H_ _36070	70														
	A068	B065	H_ _36080	80														
D074	A080	B077	H_ _36090	90														
D088			H_ _36100	100														
		B096	H_ _36110	110														
	A104		H_ _36125	125														
D114	A130	B124	H_ _36150	150	4 - 4/0	225												
D143		B156	J_ _36175	175														
D169	A154		J_ _36200LY	200														
		B180	J_ _36225	225	3/0 - 350 kcmil													
	A192		J_ _36250	250														
D211	A248	B240	L_ _36400U31X	400														
D273	A312	B302			(1-2) x (2/0 - 500 kcmil)	(1-2) x 442												
D343	A360	B361	L_ _36600U31X	600														
D396		B414																
		B477	P_ _36060-PDC	600	(1-3) x (3/0 - 500 kcmil)	(1-3) x 450												
		B515	P_ _36080-PDC	800														
		B590																
		B720	P_ _36100U44A	1000	(1-4) x (3/0 - 500 kcmil)	(1-4) x 450												

TABLE 2			A.C. MOTOR WIRING																	
IQPUMP605 CONFIGURED MODEL NO. BASE NUMBER Q6C2XXXX			WITH OPTION PH, LOAD REACTOR L4			WITH OPTION P8 TERMINAL BLOCK TB3			OR, WITHOUT OPTION PH AND P8 TO A1 DRIVE TERMINALS (T1,T2,T3)		OR, WITHOUT OPTION PH AND P8 TO A1 DRIVE TERMINAL (GROUND)									
208V	240V	480V	MFG. PART NUMBER	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	MFG. PART NUMBER	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)								
		B002	RLW-03P40_	22 - 10	4.5	NDN111A-WH-P	14 - 2	32	CUSTOMER TO WIRE PER THE AC DRIVE TECHNICAL MANUAL. USE 75 °C COPPER WIRE ONLY	CUSTOMER TO SUPPLY A UL LISTED CLOSED-LOOP CONNECTOR, PER THE AC DRIVE TECHNICAL MANUAL USE 75 °C COPPER WIRE ONLY										
		B003	RLW-04P80_																	
	A004	B004	RLW-07P60_																	
D004		B007	RLW-00110_																	
D007																				
D010	A006	B011	RLW-00140_	14 - 6	16								MPDB63153	14 - 8 OR 6 - 2/0	50 OR 120	CUSTOMER TO SUPPLY A UL LISTED CLOSED-LOOP CONNECTOR, PER THE AC DRIVE TECHNICAL MANUAL USE 75 °C COPPER WIRE ONLY				
D016	A009	B014	RLW-00210_																	
	A015		RLW-00280_																	
	A022																			
D024	A028	B021	RLW-00350_																	
		B027		6 - 4 OR 2 - 1/0	45 OR 50												MPDB67003	6 - 350	275	
D030		B034	RLW-00460_																	
	A042	B040	RLW-00550_																	
D046		B052	RLW-00650_																	
D059	A054	B065	RLW-00830_																	
D074	A080	B077	RLW-01040_	2 OR 1/0 - 2/0 OR 4/0	150 OR 180 OR 250															MPDB63153
D088	A068	B096	RLW-01300_																	
	A104																			
		B124	RL-13002																	
D114			RLW-01600_																	
D143	A130	B156	RLW-02000_	2/0 OR 3/0 - 4/0 OR 250 - 350 OR 500	180 OR 250 OR 325 OR 375	MPDB67003	6 - 350 kcmil	275												
	A154																			
D169		B180	RLW-02500_																	
	A192																			
D211	A248	B240	RLW-03220_																	
D273			RLW-04140_	(1-2) x (6 - 350 kcmil)	(1-2) x 275				MPDB67523				(1-2) x (6) OR (4) OR (3 - 4/0)	(1-2) x 80 OR 100 OR 150						
	A312	B302																		
D343	A360	B361	RLW-05150_																	
D396																				
		B414	RLW-06000_												CUSTOMER TO SUPPLY A UL LISTED CLOSED-LOOP CONNECTOR		16500-3	(1-2) x (6 - 350 kcmil)	(1-2) x 275	
		B477																		
		B515	RLW-07500_																	
		B590																		
		B720	RL-75002																	
				CUSTOMER TO SUPPLY A UL LISTED CLOSED-LOOP CONNECTOR						16528-3	(1-2) x (2 - 600 kcmil)	(1-2) x 500								
				CUSTOMER TO SUPPLY A UL LISTED CLOSED-LOOP CONNECTOR		PDB-55-500-1	(1-5) x (3/0 - 500 kcmil)	(1-5) x 450												

TABLE 3			EARTH GROUND WIRING			
IQPUMP605 CONFIGURED MODEL NO. BASE NUMBER Q6C2XXXX			INPUT GROUND LUG		MOTOR CONNECTION GROUND WITH OPTION PH OR P8	
208V	240V	480V	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)	WIRE SIZE RANGE (AWG)	TIGHTENING TORQUE (LB.-IN.)
D004	A004	B002	14 - 10	35	14 - 10	35
D007	A006	B003	OR	OR	OR	OR
D010	A009	B004	8	40	8	40
D016	A015	B007	OR	OR	OR	OR
D024	A022	B011	6 - 4	45	6 - 4	45
D030	A028	B014	OR	OR	OR	OR
D046	A042	B021	2	50	2	50
D059	A054	B027				
D074	A068	B034				
D088	A080	B040				
D114	A104	B052				
	A130	B065				
		B077				
		B096				
		B124				
D143	A154	B156	14 - 2/0	120	14 - 2/0	120
D169	A192	B180				
D211	A248	B240				
D273	A312	B302				
D343	A360	B361	6 - 250	275	6 - 250	275
D396		B414				
		B477				
		B515				
		B590				
		B720				

					YASKAWA THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.	DRAWN BY: K. PEOPLES		DATE: 10/8/25		TITLE: CUSTOMER CONNECTION IQPUMP605 CONFIGURED TYPE 12		
						CHECKED: E. ACKERMAN		DATE: 10/8/25		SIZE: C REVISION: 00 PAGE: 1 of 1		
						TECH:		DATE:				
						APPROVED: R. JENSEN		DATE: 10/8/25		DRAWING #: UDE00809		
						ORIGINAL DESIGN: K. PEOPLES		DATE: 10/8/25				
REVISIONS												
REV.	DESCRIPTION				ECO #	DRAWN BY	DATE					
00	INITIAL RELEASE				-	KAP	10/8/25					