



C/C: FP65□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2211□□□	200 TO 240	64 (140)	2
2273□□□		67 (147)	2
4180□□□	380 TO 480	66 (145)	2
4240□□□		68 (149)	2
4302□□□		71 (156)	2

□ denotes A-Z



C/C: FP65□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2211□□□	R/L1, S/L2, T/L3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
2273□□□	U/T1, V/T2, W/T3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
4180□□□	-, +1	2 - 250 x 2P (35 - 120 x 2P)	M10	20 (177)
4240□□□	⊕	2 - 350 (35 - 185)	M10	18 - 23 (159 - 204)
4302□□□				

□ Denotes A-Z
 Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA

UNITS MM [IN]
 SCALE 1:8


DRWN. J. MATTAS 6-23-22
 CHKD. J. PIOTROWSKI 6-30-22
 TECH. L. UDDIN 7-1-22
 APRV. J. CAIRO 7-19-22

TITLE
 FP605 DIMENSION DRAWING
 FRAME SIZE 9
 BACKSIDE TYPE 12 ENCLOSURE

SIZE A PAGE 2 OF 3
 DWG.NO. DD.FP605.FR9.FLNG

REV
 0


Panel Cutout



Notes:

Exposed heatsink minimum clearance D = 165 [6.50].
 Refer to Type 12 heatsink external installation manual for additional details.

YASKAWA


 UNITS MM [IN]
 SCALE 1:8

DRWN.	J. MATTAS	6-23-22
CHKD.	J. PIOTROWSKI	6-30-22
TECH.	L. UDDIN	7-1-22
APRV.	J. CAIRO	7-19-22

TITLE	FP605 DIMENSION DRAWING FRAME SIZE 9 BACKSIDE TYPE 12 ENCLOSURE
-------	---

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.FP605.FR9.FLNG		

REV	0
-----	---