

The dimensions shown are for an IP20 drive that has been converted to a UL Type 1 drive by adding the parts from UL Type 1 kit part number ZBAA-GA50V1-1

C/C: GA50□	INPUT VOLTAGE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2004□□□	200 TO 240 3-PHASE	1.0 (2.1)	0

□ denotes A-Z

YASKAWA

UNITS MM [IN]
SCALE 1:2


DRWN. J. MATTAS 10-18-19
CHKD. J. PIOTROWSKI 11-4-19
TECH. L. UDDIN 11-18-19
APRV. J. CAIRO 11-19-19

TITLE
GA500 DIMENSION DRAWING
FRAME SIZE 1.2
UL TYPE 1 ENCLOSURE


SIZE A PAGE 1 OF 3
DWG.NO. DD.GA50.FR1.2.T1

REV 0

FRONT VIEW



BOTTOM VIEW



C/C: GA50□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2004□□□	R/L1, S/L2, T/L3	14 - 12 (2.5 - 4)	M3	0.6 - 0.8 (5 - 7)
	U/T1, V/T2, W/T3	14 - 12 (2.5 - 4)	M3	0.6 - 0.8 (5 - 7)
	-, +1, +2	14 - 12 (2.5 - 4)	M3	0.6 - 0.8 (5 - 7)
	B1, B2	14 - 12 (2.5 - 4)	M3	0.6 - 0.8 (5 - 7)
	⊕	14 (2.5)	M3.5	0.8 - 1.0 (7 - 9)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA

UNITS MM [IN]
SCALE 1:2


DRWN.	J. MATTAS	10-18-19
CHKD.	J. PIOTROWSKI	11-4-19
TECH.	L. UDDIN	11-18-19
APRV.	J. CAIRO	11-19-19

TITLE
GA500 DIMENSION DRAWING
FRAME SIZE 1.2
UL TYPE 1 ENCLOSURE

SIZE A
PAGE 2 OF 3
DWG.NO.
DD.GA50.FR1.2.T1


REV
0

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

YASKAWA



UNITS MM [IN]

SCALE 1:3

DRWN.	J. MATTAS	10-18-19
CHKD.	J. PIOTROWSKI	11-4-19
TECH.	L. UDDIN	11-18-19
APRV.	J. CAIRO	11-19-19

TITLE
GA500 DIMENSION DRAWING
FRAME SIZE 1.2
UL TYPE 1 ENCLOSURE

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.GA50.FR1.2.T1		

REV
0