

Note: Spreader bar required to avoid damage during lifting

(4)-Lifting Holes
Ø30 [Ø1.18]

Cooling fan location

Center of Gravity
Note: Dimensions shown are measured from the bottom left mounting hole

C/C: GA80□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2360□□□	200 TO 240	117 (257)	3
2415□□□		120 (264)	3
4371□□□	380 TO 480	123 (271)	2
4414□□□		127 (279)	3
5289□□□	500 TO 600	127 (279)	3

□ denotes A-Z

1	ADDED 600V DRIVES
0	INITIAL RELEASE





UNITS MM [IN]
SCALE 1:12

DRWN.	J. MATTAS	4-9-19
CHKD.	J. PIOTROWSKI	5-6-19
TECH.	L. UDDIN	5-20-19
APRV.	J. CAIRO	6-13-19

TITLE
GA800 DIMENSION DRAWING
FRAME SIZE 10
BACKSIDE TYPE 12 ENCLOSURE

SIZE	A	PAGE	1 OF 3
DWG.NO.	DD.GA80.FR10.FLNG		

REV
1



C/C: GA80□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2360□□□	R/L1, S/L2, T/L3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
2415□□□	U/T1, V/T2, W/T3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
4371□□□	-, +1, +3	4/0 - 400 x 2P (120 - 205 x 2P)	M12	35 (310)
4414□□□	⊕	1 - 350 (120 - 240)	M12	32 - 40 (283 - 354)
5289□□□				

□ Denotes A-Z
 Note: Refer to applicable codes and standards for proper wire type and size.

1	ADDED 600V DRIVES
0	INITIAL RELEASE




UNITS MM [IN]
 SCALE 1:10

DRWN.	J. MATTAS	4-9-19
CHKD.	J. PIOTROWSKI	5-6-19
TECH.	L. UDDIN	5-20-19
APRV.	J. CAIRO	6-13-19

TITLE
 GA800 DIMENSION DRAWING
 FRAME SIZE 10
 BACKSIDE TYPE 12 ENCLOSURE

SIZE	A	PAGE	2 OF 3
DWG.NO.	DD.GA80.FR10.FLNG		

REV
 1



8				DRWN. J. MATTAS	4-9-19	TITLE GA800 DIMENSION DRAWING FRAME SIZE 10 BACKSIDE TYPE 12 ENCLOSURE	SIZE A	PAGE 3 OF 3	REV
				CHKD. J. PIOTROWSKI	5-6-19		DWG.NO.		1
1	ADDED 600V DRIVES			TECH. L. UDDIN	5-20-19		DD.GA80.FR10.FLNG		
0	INITIAL RELEASE			APRV. J. CAIRO	6-13-19				