



C/C:	INPUT VOLTAGE	WEIGHT	COOLING
FP65□	3-PHASE (VAC)	Kg (lb)	FANS
4477□□□	380 TO 480	192 (422)	2
4515□□□		192 (422)	2
4590□□□		203 (447)	2
4720□□□		201 (442)	3

□ denotes A-Z



C/C: FP65□	TERMINAL SYMBOL	WIRE RANGE AWG (mm <sup>2</sup> )	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
4477□□□	R/L11, S/L21, T/L31,	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
4515□□□	R/L1, S/L2, T/L3			
4590□□□	U/T1, V/T2, W/T3,	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
4720□□□	U/T1, V/T2, W/T3			
	- , +1, - , +1	3/0 - 400 x 2P (95 - 205 x 2P)	M12	35 (310)
	⊕	1/0 - 300 (50 - 150)	M12	32 - 40 (283 - 354)

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

**YASKAWA**


UNITS MM [IN]  
SCALE 1:10

DRWN. J. MATTAS 6-23-22  
CHKD. J. PIOTROWSKI 6-30-22  
TECH. L. UDDIN 7-1-22  
APRV. J. CAIRO 7-19-22

TITLE  
FP605 DIMENSION DRAWING  
FRAME SIZE 11  
BACKSIDE TYPE 12 ENCLOSURE

SIZE A PAGE 2 OF 3  
DWG.NO.  
DD.FP605.FR11.FLNG

REV  
0



Notes:  
 Exposed heatsink minimum clearance D = 225 [8.86].  
 Refer to Type 12 heatsink external installation manual for additional details.

<b>YASKAWA</b>		DRWN. J. MATTAS	6-23-22	TITLE FP605 DIMENSION DRAWING FRAME SIZE 11 BACKSIDE TYPE 12 ENCLOSURE	SIZE A	PAGE 3 OF 3	REV <b>0</b>
	UNITS MM [IN]	CHKD. J. PIOTROWSKI	6-30-22		DWG.NO.		
	SCALE 1:12	TECH. L. UDDIN	7-1-22		<b>DD.FP605.FR11.FLNG</b>		
	APRV. J. CAIRO	7-19-22					