


THERMOSTAT  
(SPDT- 1 & 2 ARE N.O./  
1 & 3 ARE N.C.)


LEFT SIDE VIEW




TWO, FOUR OR SIX POINT  
TERMINAL BLOCK

NOTE: ORIENTATION OF THERMOSTAT  
AND TERMINAL BLOCK MAY VARY


FRONT VIEW




TOP VIEW




TERMINAL DESIGNATIONS



SINGLE RESISTOR



DOUBLE RESISTOR




TRIPLE RESISTOR



ENCLOSURE	W1	W2	W3	D1	D2	D3	H	EST. WEIGHT (LBS)
GCE1	12-1/2	12	10-1/2	5-1/8	5	---	5	7
GCE2	12-1/2	12	10-1/2	7-1/8	7	4-1/2	5	9
GCE3	12-1/2	12	10-1/2	10-1/8	10	7-1/2	5	13
GCE4	12-1/2	12	10-1/2	13-1/8	13	10-1/2	5	16
GCE5	12-1/2	12	10-1/2	16-1/8	16	13-1/2	5	18
GCE6	19-1/2	19	17-1/2	10-1/8	10	7-1/2	5	20
GCE8	19-1/2	19	17-1/2	13-1/8	13	10-1/2	5	25
GCE9	27	26-1/2	25	10-1/8	10	7-1/2	5	28
GCE10	19-1/2	19	17-1/2	16-1/8	16	13-1/2	5	30
GCE12	27	26-1/2	25	13-1/8	13	10-1/2	5	35
GCE15	27	26-1/2	25	16-1/8	16	13-1/2	5	38
GCE18	28-1/2	28	26-1/2	10-1/8	10	7-1/2	10	44
GCE24	28-1/2	28	26-1/2	13-1/8	13	10-1/2	10	54
GCE30	28-1/2	28	26-1/2	16-1/8	16	13-1/2	10	59

**YASKAWA**



DRWN.	J. MATTAS	4-19-18
CHKD.	J. PIOTROWSKI	4-23-18
TECH.	L. UDDIN	4-24-18
APRV.	J. CAIRO	4-25-18

TITLE  
DIMENSION DRAWING  
BRAKING RESISTOR  
GCE ENCLOSURE, TYPE 1

SIZE	A	PAGE	1 OF 1
DWG.NO.	DD.GCE.01		

REV  
1

1	VARIOUS UPDATES
0	INITIAL RELEASE

UNITS	INCH
SCALE	NTS