



(3)-M12 POWER TERMINALS
 MAX CLAMPING TORQUE: 177 +/- 17.7 lb.in.
 (20 +/- 2 N.m.)



NOTES:
 1. MOUNTING ORIENTATION MUST BE SUCH THAT POWER TERMINALS ARE FACING UP
 2. OUTER SIDES MAY BE BOWED AS SHOWN

ELECTRICAL DIAGRAM



FRONT VIEW

PART #	VOLTAGE (VAC)	CURRENT (Arms)	CAPACITANCE (uF +/-10%)	FREQUENCY (HZ)	WEIGHT LBS (Kg)	HEAT LOSS (W)
UCA000063	528	133	402	50/60	73 (33)	41

FOR ADDITIONAL DETAILS AND SPECIFICATIONS, CONSULT MANUAL

TOLERANCES / REFERENCES:			DRAWN: J. MATTAS	DATE: 8-18-14	TITLE: DIMENSION DRAWING CAPACITOR UCA000063
			CHECKED: J. BORJA	DATE: 9-17-14	
		THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA, INC.	TECH: J. PIOTROWSKI	DATE: 9-17-14	
UNITS: IN [mm]	SCALE: 1:5		APPROVED: J. CAIRO	DATE: 9-22-14	SIZE: A
		ORIGINAL DESIGN: -	DATE: -	DRAWING #: DD.UCA000063	PAGE: 1 of 1