



CONTROL TRANSFORMER PRIMARY CONNECTIONS		
INPUT VOLTS	TERMINALS	JUMPER LOCATION
230/240	(H1)	(H1) TO (H3)
460/480	(H1)	(H2) TO (H4)
600	(H1)	(H2) TO (H3)
		NONE

CONTACT SEQUENCE CHART FOR S2				
CONTACT	POSITION		MANUF. LOCATION /TYPE	
	HAND	AUTO	1RO	1LO
1	X			
2		X		
3	X			

\* SCHEMATIC SHOWS THIS POSITION.

CONTACT SEQUENCE CHART FOR S2				
CONTACT	POSITION		MANUF. LOCATION /TYPE	
	HAND	AUTO	1RO	1LO
1	X			
2		X		
3			X	

\* SCHEMATIC SHOWS THIS POSITION.

- NOTES:
- CONNECTED TO THE CABINET. CUSTOMER TO CONNECT THE CABINET GROUND LUGS TO EARTH GROUND AND UTILITY GROUND.
  - CONDUIT FITTINGS/HUBS SHALL COMPLY WITH THE 'STANDARD FOR CONDUIT, TUBING, AND CABLE FITTINGS, UL 514B'.
  - WITHOUT THE CIRCUIT BREAKER (OPTION PC OR PE), OR DISCONNECT SWITCH OPTION PD, THE DISCONNECT MEANS MUST BE SUPPLIED BY THE CUSTOMER.
  - BRANCH CIRCUIT PROTECTION TO BE SUPPLIED BY THE CUSTOMER WHEN NOTED ON THE CABINET DATA NAMEPLATE.
  - INSULATED TWISTED SHIELDED WIRE IS REQUIRED. SHIELD TO CONNECT TO PROPER TERMINALS AS SHOWN. CONNECT THE SHIELD ONLY AT THIS END. STUB AND ISOLATE THE OTHER END. DO NOT RUN THESE WIRES IN THE SAME CONDUIT AS THE AC POWER AND AC CONTROL WIRES. KEEP ALL WIRING UNDER 50m IN LENGTH.
  - CUSTOMER TO ADJUST THE THERMOSTAT ON THE SPACE HEATER HR1 FOR THE MINIMUM DESIRED TEMPERATURE INSIDE THE DRIVE CABINET. THIS SET TEMPERATURE IS NORMALLY SELECTED TO BE SLIGHTLY HIGHER THAN THE MINIMUM AMBIENT TEMPERATURE OF THE AIR SURROUNDING THE CABINET, AND IS THE TEMPERATURE AT WHICH THE SPACE HEATER HR1 WILL SHUT OFF.
  - FOR A CONTROL TRANSFORMER T1 POWER RATING OF 350VA OR GREATER, SECONDARY FUSE F6 IS ADDED.
  - IF AC MOTOR IS FURNISHED WITH A N.C. THERMAL SWITCH THEN SET DRIVE PARAMETER H1-08 TO 27. THIS WILL CAUSE THE DRIVE TO COAST TO STOP UPON AN AC MOTOR THERMAL FAULT.
  - ALONG WITH THIS, ADD THE FOLLOWING CUSTOMER WIRING: WIRE THE N.C. THERMAL SWITCH BETWEEN DRIVE TERMINALS S8 AND SN, AS PER NOTE 5 ABOVE.
  - OPTIONS TD, IG, TH, OR TQ CONTROL (SEE UDE00338 FOR MORE INFORMATION)

\* - INDICATES COMPONENTS NOT SUPPLIED BY YASKAWA.  
 - - INDICATES CUSTOMER WIRING.  
 SEE DRAWING UDE00345 FOR CUSTOMER CONNECTION TABLES.  
 SEE DRAWING UDE00338 FOR DRIVE PARAMETER SETTINGS.

**YASKAWA**

THIS DOCUMENT AND INFORMATION CONTAINED HEREIN IS UNCLASSIFIED AND NOT BE RELEASED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA, INC.

REV.	DESCRIPTION	ECO #	DATE	DATE	DATE
04	UPDATE CUSTOMER CONNECTIONS TO BOLD LINES	6620	DJP	10/07/15	
03	ADDED FM, AM, MP TERMINALS TO DRIVE	6422	DJP	07/17/15	

REVISIONS

REV.	DESCRIPTION	ECO #	DATE	DATE	DATE
04	UPDATE CUSTOMER CONNECTIONS TO BOLD LINES	6620	DJP	10/07/15	
03	ADDED FM, AM, MP TERMINALS TO DRIVE	6422	DJP	07/17/15	

SCHEMATIC DIAGRAM  
 A1000 CONFIGURED  
 HEAVY DUTY RATING  
 TYPE 3R