

C/C: GA80□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2018□□□	200 TO 240	3.9 (8.6)	1
2021□□□		3.9 (8.6)	1
2030□□□		4.2 (9.2)	2
2042□□□		4.2 (9.2)	2
4007□□□	380 TO 480	3.9 (8.6)	1
4009□□□		3.9 (8.6)	1
4012□□□		3.9 (8.6)	1
4018□□□		4.2 (9.2)	2
4023□□□		4.2 (9.2)	2

□ denotes A-Z

1	REVISED MOUNTING BKTS P2
0	INITIAL RELEASE




UNITS MM [IN]
 SCALE 1:5

DRWN.	J. MATTAS	4-3-19
CHKD.	J. PIOTROWSKI	5-6-19
TECH.	L. UDDIN	5-20-19
APRV.	J. CAIRO	6-13-19

TITLE
 GA800 DIMENSION DRAWING
 FRAME SIZE 1.5
 BACKSIDE TYPE 12 ENCLOSURE

SIZE	A	PAGE	1 OF 3
DWG.NO.	DD.GA80.FR1.5.FLNG		



Notes:
 Exposed heatsink minimum clearance D = 78 [3.07].
 Refer to Type 12 heatsink external installation manual for additional details.

1	REVISED MOUNTING BKTS P2
0	INITIAL RELEASE



	DRWN.	J. MATTAS	4-3-19
	CHKD.	J. PIOTROWSKI	5-6-19
	TECH.	L. UDDIN	5-20-19
	APRV.	J. CAIRO	6-13-19
UNITS MM [IN]		SCALE 1:3	

TITLE	GA800 DIMENSION DRAWING FRAME SIZE 1.5 BACKSIDE TYPE 12 ENCLOSURE
-------	---

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.GA80.FR1.5.FLNG		

REV	1
-----	---