



C/C: HV60□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2075□□□	200 TO 240	41 (90.4)	2
2088□□□		41 (90.4)	2
2114□□□		44 (97.0)	2
4077□□□	380 TO 480	44 (97.0)	2
4096□□□		46 (101.4)	2

□ denotes A-Z

<b>YASKAWA</b>		DRWN. J. MATTAS 4-9-21	TITLE HV600 DIMENSION DRAWING	SIZE A	PAGE 1 OF 3	REV <b>0</b>
	UNITS MM [IN]	CHKD. J. PIOTROWSKI 5-17-21	FRAME SIZE 4	DWG.NO. <b>DD.HV60.FR4.T12.SW</b>		
	SCALE 1:12	TECH. L. UDDIN 5-27-21	IP55/UL TYPE 12 ENCLOSURE			
		APRV. J. CAIRO 5-28-21	WITH MAIN SWITCH			



**EMC FILTER SWITCHES**



C/C: HV60□	TERMINAL SYMBOL	WIRE RANGE AWG (mm <sup>2</sup> )	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2075□□□	R/L1, S/L2, T/L3	8 - 2/0 (10 - 70)	M8	15 - 22 (132.8 - 194.7)
2088□□□	U/T1, V/T2, W/T3	8 - 2/0 (10 - 70)	M8	5.4 - 6.0 (47.8 - 53.1)
2114□□□	⊕	8 - 2/0 (10 - 70)	M8	9.0 - 11.0 (79.7 - 97.4)
4077□□□				
4096□□□				

□ Denotes A-Z  
Note: Refer to applicable codes and standards for proper wire type and size.



UNITS MM [IN]  
SCALE 1:8


DRWN. J. MATTAS 4-9-21  
CHKD. J. PIOTROWSKI 5-17-21  
TECH. L. UDDIN 5-27-21  
APRV. J. CAIRO 5-28-21

TITLE  
HV600 DIMENSION DRAWING  
FRAME SIZE 4  
IP55/UL TYPE 12 ENCLOSURE  
WITH MAIN SWITCH


SIZE A PAGE 2 OF 3  
DWG.NO. DD.HV60.FR4.T12.SW

REV 0

Minimum Installation Clearances



**YASKAWA**

  
 UNITS MM [IN]  
 SCALE 1:8

DRWN.	J. MATTAS	4-9-21
CHKD.	J. PIOTROWSKI	5-17-21
TECH.	L. UDDIN	5-27-21
APRV.	J. CAIRO	5-28-21

TITLE  
 HV600 DIMENSION DRAWING  
 FRAME SIZE 4  
 IP55/UL TYPE 12 ENCLOSURE  
 WITH MAIN SWITCH

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.HV60.FR4.T12.SW		

REV	0
-----	---