



Product Service

EC-Statement of Compliance

No. E6 09 10 22021 348

Holder of Certificate: Yaskawa Electric Corp.
Tokyo Plant
480 Kamifujisawa, Iruma
Saitama 358-8555
JAPAN

Name of Object: AC servo systems
AC Servo Motor

Model(s): JUNMA Series
(SJME-**AM*****)
SJME-01A*****, SJME-02A*****,
SJME-04A*****, SJME-08A*****)
(See Attachment for Nomenclature)

Description of Object:

Rated Voltage:	200 VAC, 3 phase
Rated Power:	100 W-750 W
Protection Class:	I

Tested according to: EN 55011/A2:2007, Group 1, Class A;
EN 61000-6-2:2005

This EC-Statement of Compliance is issued according to the Directive 2004/108/EC relating to electromagnetic compatibility. It confirms that the listed apparatus complies with such aspects of the essential requirements of the EMC directive as specified by the manufacturer or his authorized representative in the European Community and applies only to the sample and its technical documentation submitted to TÜV SÜD Product Service GmbH for testing and certification. See also notes overleaf.

Technical report no.: TYOEMC23409A



Date, 2009-10-15

TÜV SÜD Product Service GmbH is Notified Body to the Directive 2004/108/EC of the European Parliament and of the council with the identification number 0123.

Page 1 of 3

Attachment

Statement No. **E6 09 10 22021 348**



Product Service

SERVO MOTOR (SJME Series)

Type : SJME-xxAMxxxxx

Model Numbers

(1)Standard type

<u>SJME</u>	-	<u>01</u>	<u>A</u>	<u>M</u>	<u>A</u>	<u>2</u>	<u>1</u>	<u>-OY</u>
1		2	3	4	5	6	7	8

1.Motor type

SJME Series

2.Motor Output

01	100W
02	200W
04	400W
08	750W

3.Power Supply

A	AC200Vrms
---	-----------

4.Encoder

M	256P/R(Analogue)
---	------------------

5.Design Revision Order

A	Standard	B	Standard
C	with M17 Signal and Power connectors		

6.Shaft Type

2	Straight (without keyway)
3	Tapered 1/10(with parallel keyway)
4	Straight (with keyway)
5	Tapered 1/10(with woodruff keyway)
6	Straight (without keyway and tapped hole)
8	Straight (tapped hole)
A	Straight (with flat key seat)
B	Straight (with double flat key seat)
C	Straight (with keyway and flat key seat)

7.Optional Specifications

1	Without Option
C	With Brake (24V)
S	With Shaft Seal
E	With Brake (24V) and Shaft Seal

8.Additional type

Blank	: standard
-OY	: standard

Attachment

Statement No. **E6 09 10 22021 348**



Product Service

(2) Exclusive Design for Customer

SJME - 01 A M A - x x x x
 1 2 3 4 5 6 7 8 9

1. Motor type

SJME Series

2. Motor Output

01 100W

02 200W

04 400W

08 750W

3. Power Supply

A 200Vrms

4. Encoder

M 256P/R(Analogue)

5. Design Revision Order

A Standard B Standard

C with M17 Signal and Power connectors

6,7. Customer Cord

8,9. Design Revision Order For Customer

Model List

Model	Supply Voltage	Phase	Current(A)	Output(W)
SJME-01Axxxxxx	AC200V	3	0.84	100
SJME-02Axxxxxx	AC200V	3	1.1	200
SJME-04Axxxxxx	AC200V	3	2.0	400
SJME-08Axxxxxx	AC200V	3	3.7	750