

**A.C. INPUT**

Volts: \_\_\_\_\_ Hz: \_\_\_\_\_  
Phase: \_\_\_\_\_ Amps: \_\_\_\_\_

[-----]  
SCCR: [-----]

**A.C. OUTPUT**

Volts: \_\_\_\_\_ Hz: \_\_\_\_\_  
Phase: \_\_\_\_\_ Amps: \_\_\_\_\_

[-----]

Designator	Rating	Type
[ F1, F2		
[ F6		
[ F7		
[ F3, F4, F5		
[-----]		

Serial No.: \_\_\_\_\_  
Model No.: \_\_\_\_\_  
Type.: \_\_\_\_\_  
W.D.: \_\_\_\_\_  
Inst. Manual.: \_\_\_\_\_

SUMMARY OF PAGES		
PRODUCT	SCCR	INFO
Z1B1	PAGE 2	BYPASS TYPE 1
Z1C1	PAGE 3	CONFIGURED TYPE 1
Z1BB	PAGE 4	BYPASS TYPE 12
	PAGE 5	WITH OPTION PY
	PAGE 6	WITH OPTION PA
Z1CB	PAGE 7	WITHOUT OPTIONS PC OR PM, AND WITHOUT OPTION PF
		WITHOUT OPTIONS PC OR PM, AND WITH OPTION PF
Z1CB	PAGE 8	WITH OPTION PC
		WITH OPTION PM
Z1B3	PAGE 9	BYPASS TYPE 3R

FIGURE 1

SCCR: ① kA rms sym., ② V max.

USE FORMAT: UNPN0081-SCCR 1

SCCR: ① kA rms sym., ② V max.,  
with ③ A max., Class ④ fuses

USE FORMAT: UNPN0081-SCCR 2

SCCR: ① kA rms sym., ② V max.,  
with ③ NTD fuses

USE FORMAT: UNPN0081-SCCR 3

SCCR: ① kA rms sym., ② V max.,  
or  
③ kA rms sym., ② V max.,  
with ④ A max., Class ⑤ fuses

USE FORMAT: UNPN0081-SCCR 4

SCCR: ① kA rms sym., ② V max.,  
with ③ kAIR min., ④ A fuses or MCCB

USE FORMAT: UNPN0081-SCCR 5

SCCR: ① kA rms sym., ② V max.,  
with ③ kAIR min., ④ A max. MCCB

USE FORMAT: UNPN0081-SCCR 6

SCCR: ① kA rms sym., ② V max.,  
with ③ kAIR min., ④ A max. MCCB,  
or ③ kAIR min., ⑤ A max. Class ⑥ fuses

USE FORMAT: UNPN0081-SCCR 7

	<b>DRAWN BY:</b> K. MALUSIC	<b>DATE:</b> 5/15/12	<b>TITLE:</b> AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	<b>CHECKED:</b> K. FLIERL	<b>DATE:</b> 5/15/12			
<b>TECH:</b>	<b>DATE:</b>				
<b>APPROVED:</b> J. ZUEHLKE	<b>DATE:</b> 5/15/12	<b>SIZE:</b> C	<b>REVISION:</b> 03	<b>PAGE:</b> 1 of 9	
<b>ORIGINAL DESIGN:</b> K. FLIERL	<b>DATE:</b> 11/1/11	<b>DRAWING #:</b> UDA00727			

REVISIONS				
REV.	DESCRIPTION	ECO #	DRAWN BY	DATE
03	ADDED Z1CB AND Z1B3 PART NUMBERS	4152	DRC	5/1/13
02	ADDED Z1B1 PART NUMBERS	3917	DJP	1/23/13
01	ADDED Z1C1 PART NUMBERS	3431	KM	5/15/12

THIS DOCUMENT AND INFORMATION  
CONTAINED IN IT ARE CONFIDENTIAL,  
AND CANNOT BE COPIED OR  
DISCLOSED IN WHOLE OR IN PART  
WITHOUT THE EXPRESS WRITTEN  
CONSENT OF YASKAWA AMERICA INC.

TABLE 1								
WORK ORDER PART NO. BEGINNING	WITHOUT OPTION PM					WITH OPTION PM		
	USE FORMAT UNPN0081-SCCR_	①	②	③	④	USE FORMAT UNPN0081-SCCR_	①	②
Z1B1B001	2	100	480	30	J	1	100	480
Z1B1B002	2	100	480	30	J	1	100	480
Z1B1B003	2	100	480	30	J	1	100	480
Z1B1B004	2	100	480	30	J	1	100	480
Z1B1B007	2	100	480	30	J	1	100	480
Z1B1B011	2	100	480	30	J	1	100	480
Z1B1B014	2	100	480	30	J	1	100	480
Z1B1B021	2	100	480	60	J	1	100	480
Z1B1B027	2	100	480	60	J	1	100	480
Z1B1B034	2	100	480	60	J	1	100	480
Z1B1B040	2	100	480	100	J	1	100	480
Z1B1B052	2	100	480	100	J	1	100	480
Z1B1B065	2	100	480	200	J	1	100	480
Z1B1B077	2	100	480	150	J	1	100	480
Z1B1B096	2	100	480	150	J	1	100	480
Z1B1B124	2	100	480	175	J	1	100	480
Z1B1B156	2	100	480	250	J	1	100	480
Z1B1B180	2	100	480	250	J	1	100	480
Z1B1B240	2	100	480	400	J	1	100	480
Z1B1B302	2	100	480	600	J	1	100	480
Z1B1B361	2	100	480	600	J	1	100	480
Z1B1B414	2	100	480	600	J	1	100	480
Z1B1B477	2	100	480	800	L	1	100	480
Z1B1B515	2	100	480	800	L	1	100	480
Z1B1B590	2	100	480	1000	L	1	100	480
Z1B1D002	2	100	208	30	J	1	100	208
Z1B1D003	2	100	208	30	J	1	100	208
Z1B1D004	2	100	208	30	J	1	100	208
Z1B1D006	2	100	208	30	J	1	100	208
Z1B1D007	2	100	208	30	J	1	100	208
Z1B1D010	2	100	208	30	J	1	100	208
Z1B1D016	2	100	208	30	J	1	100	208
Z1B1D024	2	100	208	60	J	1	100	208
Z1B1D030	2	100	208	60	J	1	100	208
Z1B1D046	2	100	208	100	J	1	100	208
Z1B1D059	2	100	208	100	J	1	100	208
Z1B1D074	2	100	208	200	J	1	100	208
Z1B1D088	2	100	208	150	J	1	100	208
Z1B1D114	2	100	208	175	J	1	100	208
Z1B1D143	2	100	208	250	J	1	100	208
Z1B1D169	2	100	208	250	J	1	100	208
Z1B1D211	2	100	208	400	J	1	100	208
Z1B1D273	2	100	208	400	J	1	100	208
Z1B1D343	2	100	208	600	J	1	100	208
Z1B1D396	2	100	208	600	J	1	100	208


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	<b>DRAWN BY:</b> K. MALUSIC	<b>DATE:</b> 5/15/12	<b>TITLE:</b> AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	<b>CHECKED:</b> K. FLIERL	<b>DATE:</b> 5/15/12			
	<b>TECH:</b>	<b>DATE:</b>			
	<b>APPROVED:</b> J. ZUEHLKE	<b>DATE:</b> 5/15/12	<b>SIZE:</b> C	<b>REVISION:</b> 03	<b>PAGE:</b> 2 of 9
<b>ORIGINAL DESIGN:</b> K. FLIERL	<b>DATE:</b> 11/1/11	<b>DRAWING #:</b> UDA00727			

TABLE 2											
WORK ORDER PART NO. BEGINNING	WITHOUT OPTION PC OR PM					WITH OPTION PC			WITH OPTION PM		
	USE FORMAT UNPN0081-SCCR_	①	②	③	④	USE FORMAT UNPN0081-SCCR_	①	②	USE FORMAT UNPN0081-SCCR_	①	②
Z1C1B001	2	100	480	3	J/RK1	1	65	480	1	100	480
Z1C1B002	2	100	480	4	J/RK1	1	65	480	1	100	480
Z1C1B003	2	100	480	6	J/RK1	1	65	480	1	100	480
Z1C1B004	2	100	480	8	J/RK1	1	65	480	1	100	480
Z1C1B007	2	100	480	12	J/RK1	1	65	480	1	100	480
Z1C1B011	2	100	480	15	J/RK1	1	65	480	1	100	480
Z1C1B014	2	100	480	20	J/RK1	1	65	480	1	100	480
Z1C1B021	2	100	480	35	J/RK1	1	65	480	1	100	480
Z1C1B027	2	100	480	45	J/RK1	1	65	480	1	100	480
Z1C1B034	2	100	480	50	J/RK1	1	65	480	1	100	480
Z1C1B040	2	100	480	70	J/RK1	1	65	480	1	100	480
Z1C1B052	2	100	480	90	J/RK1	1	65	480	1	100	480
Z1C1B065	2	100	480	110	J/RK1	1	65	480	1	100	480
Z1C1B077	2	100	480	125	J/RK1	1	65	480	1	100	480
Z1C1B096	2	100	480	150	J/RK1	1	65	480	1	100	480
Z1C1B124	5	100	480	100	150	1	65	480	1	100	480
Z1C1B156	5	100	480	100	250	1	65	480	1	100	480
Z1C1B180	5	100	480	100	250	1	65	480	1	100	480
Z1C1B240	5	100	480	100	400	1	65	480	1	100	480
Z1C1B302	5	100	480	100	400	1	65	480	1	100	480
Z1C1B361	5	100	480	100	600	1	65	480	1	100	480
Z1C1B414	5	100	480	100	600	1	65	480	1	100	480
Z1C1B477	5	100	480	100	800	1	65	480	1	100	480
Z1C1B515	5	100	480	100	800	1	65	480	1	100	480
Z1C1B590	5	100	480	100	800	1	65	480	1	100	480
Z1C1D002	2	100	208	4	J/RK1	1	65	208	1	100	208
Z1C1D003	2	100	208	6	J/RK1	1	65	208	1	100	208
Z1C1D004	2	100	208	8	J/RK1	1	65	208	1	100	208
Z1C1D006	2	100	208	10	J/RK1	1	65	208	1	100	208
Z1C1D007	2	100	208	12	J/RK1	1	65	208	1	100	208
Z1C1D010	2	100	208	15	J/RK1	1	65	208	1	100	208
Z1C1D016	2	100	208	25	J/RK1	1	65	208	1	100	208
Z1C1D024	2	100	208	40	J/RK1	1	65	208	1	100	208
Z1C1D030	2	100	208	50	J/RK1	1	65	208	1	100	208
Z1C1D046	2	100	208	80	J/RK1	1	65	208	1	100	208
Z1C1D059	2	100	208	100	J/RK1	1	65	208	1	100	208
Z1C1D074	2	100	208	125	J/RK1	1	65	208	1	100	208
Z1C1D088	2	100	208	150	J/RK1	1	65	208	1	100	208
Z1C1D114	5	100	208	100	150	1	65	208	1	100	208
Z1C1D143	5	100	208	100	250	1	65	208	1	100	208
Z1C1D169	5	100	208	100	250	1	65	208	1	100	208
Z1C1D211	5	100	208	100	400	1	65	208	1	100	208
Z1C1D273	5	100	208	100	400	1	65	208	1	100	208
Z1C1D343	5	100	208	100	600	1	65	208	1	100	208
Z1C1D396	5	100	208	100	600	1	65	208	1	100	208


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 5/15/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	CHECKED: K. FLIERL	DATE: 5/15/12			
	TECH:	DATE:			
	APPROVED: J. ZUEHLKE	DATE: 5/15/12	SIZE: C	REVISION: 03	PAGE: 3 of 9
ORIGINAL DESIGN: K. FLIERL	DATE: 11/1/11	DRAWING #: UDA00727			

TABLE 3								
WORK ORDER PART NO. BEGINNING	USE FORMAT UNPN0081-SCCR_	WITHOUT OPTION PM				WITH OPTION PM		
		①	②	③	④	USE FORMAT UNPN0081-SCCR_	①	②
Z1BBB001	2	100	480	30	J	1	100	480
Z1BBB002	2	100	480	30	J	1	100	480
Z1BBB003	2	100	480	30	J	1	100	480
Z1BBB004	2	100	480	30	J	1	100	480
Z1BBB007	2	100	480	30	J	1	100	480
Z1BBB011	2	100	480	30	J	1	100	480
Z1BBB014	2	100	480	30	J	1	100	480
Z1BBB021	2	100	480	60	J	1	100	480
Z1BBB027	2	100	480	60	J	1	100	480
Z1BBB034	2	100	480	60	J	1	100	480
Z1BBB040	2	100	480	100	J	1	100	480
Z1BBB052	2	100	480	100	J	1	100	480
Z1BBB065	2	100	480	200	J	1	100	480
Z1BBB077	2	100	480	150	J	1	100	480
Z1BBB096	2	100	480	150	J	1	100	480
Z1BBB124	2	100	480	175	J	1	100	480
Z1BBB156	2	100	480	250	J	1	100	480
Z1BBB180	2	100	480	250	J	1	100	480
Z1BBB240	2	100	480	400	J	1	100	480
Z1BBB302	2	100	480	600	J	1	100	480
Z1BBB361	2	100	480	600	J	1	100	480
Z1BBB414	2	100	480	600	J	1	100	480
Z1BBB477	2	100	480	800	L	1	100	480
Z1BBB515	2	100	480	800	L	1	100	480
Z1BBB590	2	100	480	1000	L	1	100	480
Z1BBD002	2	100	208	30	J	1	100	208
Z1BBD003	2	100	208	30	J	1	100	208
Z1BBD004	2	100	208	30	J	1	100	208
Z1BBD006	2	100	208	30	J	1	100	208
Z1BBD007	2	100	208	30	J	1	100	208
Z1BBD010	2	100	208	30	J	1	100	208
Z1BBD016	2	100	208	30	J	1	100	208
Z1BBD024	2	100	208	60	J	1	100	208
Z1BBD030	2	100	208	60	J	1	100	208
Z1BBD046	2	100	208	100	J	1	100	208
Z1BBD059	2	100	208	100	J	1	100	208
Z1BBD074	2	100	208	200	J	1	100	208
Z1BBD088	2	100	208	150	J	1	100	208
Z1BBD114	2	100	208	175	J	1	100	208
Z1BBD143	2	100	208	250	J	1	100	208
Z1BBD169	2	100	208	250	J	1	100	208
Z1BBD211	2	100	208	400	J	1	100	208
Z1BBD273	2	100	208	400	J	1	100	208
Z1BBD343	2	100	208	600	J	1	100	208
Z1BBD396	2	100	208	600	J	1	100	208


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 5/15/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	CHECKED: K. FLIERL	DATE: 5/15/12			
	TECH:	DATE:			
	APPROVED: J. ZUEHLKE	DATE: 5/15/12	SIZE: C	REVISION: 03	PAGE: 4 of 9
ORIGINAL DESIGN: K. FLIERL	DATE: 11/1/11	DRAWING #: UDA00727			

TABLE 4								
WORK ORDER PART NO. BEGINNING	WITHOUT OPTION PM, WITH OPTION PA					WITH OPTION PM AND PA		
	USE FORMAT UNPN0081-SCCR_	①	②	③	④	USE FORMAT UNPN0081-SCCR_	①	②
Z1BBB001	2	100	480	25	J	1	100	480
Z1BBB002	2	100	480	30	J	1	100	480
Z1BBB003	2	100	480	30	J	1	100	480
Z1BBB004	2	100	480	30	J	1	100	480
Z1BBB007	2	100	480	30	J	1	100	480
Z1BBB011	2	100	480	30	J	1	100	480
Z1BBB014	2	100	480	30	J	1	100	480
Z1BBB021	2	100	480	60	J	1	100	480
Z1BBB027	2	100	480	60	J	1	100	480
Z1BBB034	2	100	480	100	J	1	100	480
Z1BBB040	2	100	480	100	J	1	100	480
Z1BBB052	2	100	480	100	J	1	100	480
Z1BBB065	2	100	480	200	J	1	100	480
Z1BBB077	2	100	480	150	J	1	100	480
Z1BBB096	2	100	480	200	J	1	100	480
Z1BBB124	2	100	480	250	J	1	100	480
Z1BBB156	3	100	480	400	-	1	100	480
Z1BBB180	3	100	480	450	-	1	100	480
Z1BBB240	3	100	480	800	-	1	100	480
Z1BBB302	3	100	480	1000	-	1	100	480
Z1BBB361	3	100	480	1000	-	1	100	480
Z1BBB414	3	100	480	1000	-	1	100	480
Z1BBB477	3	100	480	1200	-	1	100	480
Z1BBB515	3	100	480	1200	-	1	100	480
Z1BBB590	3	100	480	1200	-	1	100	480
Z1BBD002	2	100	208	30	J	1	100	208
Z1BBD003	2	100	208	30	J	1	100	208
Z1BBD004	2	100	208	30	J	1	100	208
Z1BBD006	2	100	208	30	J	1	100	208
Z1BBD007	2	100	208	30	J	1	100	208
Z1BBD010	2	100	208	30	J	1	100	208
Z1BBD016	2	100	208	35	J	1	100	208
Z1BBD024	2	100	208	60	J	1	100	208
Z1BBD030	2	100	208	80	J	1	100	208
Z1BBD046	2	100	208	100	J	1	100	208
Z1BBD059	2	100	208	125	J	1	100	208
Z1BBD074	2	100	208	150	J	1	100	208
Z1BBD088	2	100	208	175	J	1	100	208
Z1BBD114	2	100	208	250	J	1	100	208
Z1BBD143	3	100	208	400	-	1	100	208
Z1BBD169	3	100	208	450	-	1	100	208
Z1BBD211	3	100	208	800	-	1	100	208
Z1BBD273	3	100	208	1000	-	1	100	208
Z1BBD343	3	100	208	1000	-	1	100	208
Z1BBD396	3	100	208	1000	-	1	100	208


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	<b>DRAWN BY:</b> K. MALUSIC	<b>DATE:</b> 5/15/12	<b>TITLE:</b> AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	<b>CHECKED:</b> K. FLIERL	<b>DATE:</b> 5/15/12			
	<b>TECH:</b>	<b>DATE:</b>			
	<b>APPROVED:</b> J. ZUEHLKE	<b>DATE:</b> 5/15/12	<b>SIZE:</b> C	<b>REVISION:</b> 03	<b>PAGE:</b> 5 of 9
<b>ORIGINAL DESIGN:</b> K. FLIERL	<b>DATE:</b> 11/1/11	<b>DRAWING #:</b> UDA00727			

TABLE 5								
WORK ORDER PART NO. BEGINNING	WITHOUT OPTION PM, WITH OPTION PY					WITH OPTION PM AND PY		
	USE FORMAT UNPN0081-SCCR_	①	②	③	④	USE FORMAT UNPN0081-SCCR_	①	②
Z1BBB001	2	100	480	30	J	1	100	480
Z1BBB002	2	100	480	30	J	1	100	480
Z1BBB003	2	100	480	30	J	1	100	480
Z1BBB004	2	100	480	30	J	1	100	480
Z1BBB007	2	100	480	30	J	1	100	480
Z1BBB011	2	100	480	30	J	1	100	480
Z1BBB014	2	100	480	30	J	1	100	480
Z1BBB021	2	100	480	60	J	1	100	480
Z1BBB027	2	100	480	60	J	1	100	480
Z1BBB034	2	100	480	60	J	1	100	480
Z1BBB040	2	100	480	100	J	1	100	480
Z1BBB052	2	100	480	100	J	1	100	480
Z1BBB065	2	100	480	100	J	1	100	480
Z1BBB077	2	100	480	200	J	1	100	480
Z1BBB096	2	100	480	400	J	1	100	480
Z1BBB124	2	100	480	250	J	1	100	480
Z1BBB156	2	100	480	250	J	1	100	480
Z1BBB180	2	100	480	250	J	1	100	480
Z1BBB240	2	100	480	600	J	1	100	480
Z1BBB302	2	100	480	600	J	1	100	480
Z1BBB361	2	100	480	600	J	1	100	480
Z1BBB414	3	18	480	1000	-	1	100	480
Z1BBB477	3	30	480	1000	-	1	100	480
Z1BBB515	3	30	480	1000	-	1	100	480
Z1BBB590	3	30	480	1000	-	1	100	480
Z1BBD002	2	100	208	30	J	1	100	208
Z1BBD003	2	100	208	30	J	1	100	208
Z1BBD004	2	100	208	30	J	1	100	208
Z1BBD006	2	100	208	30	J	1	100	208
Z1BBD007	2	100	208	30	J	1	100	208
Z1BBD010	2	100	208	30	J	1	100	208
Z1BBD016	2	100	208	30	J	1	100	208
Z1BBD024	2	100	208	60	J	1	100	208
Z1BBD030	2	100	208	60	J	1	100	208
Z1BBD046	2	100	208	100	J	1	100	208
Z1BBD059	2	100	208	100	J	1	100	208
Z1BBD074	2	100	208	200	J	1	100	208
Z1BBD088	2	100	208	400	J	1	100	208
Z1BBD114	2	100	208	400	J	1	100	208
Z1BBD143	2	100	208	400	J	1	100	208
Z1BBD169	2	100	208	250	J	1	100	208
Z1BBD211	2	100	208	600	J	1	100	208
Z1BBD273	2	100	208	600	J	1	100	208
Z1BBD343	2	100	208	600	J	1	100	208
Z1BBD396	3	18	208	1000	-	1	100	208


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 5/15/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	CHECKED: K. FLIERL	DATE: 5/15/12			
	TECH:	DATE:			
	APPROVED: J. ZUEHLKE	DATE: 5/15/12	SIZE: C	REVISION: 03	PAGE: 6 of 9
ORIGINAL DESIGN: K. FLIERL	DATE: 11/1/11	DRAWING #: UDA00727			

TABLE 6										
WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC OR PM, AND									
	USE FORMAT UNPN0081-SCCR_	WITHOUT OPTION PF						WITH OPTION PF		
		①	②	③	④	⑤	⑥	USE FORMAT UNPN0081-SCCR_	①	②
Z1CBB001	7	100	480	100	15	1	J, T, CC	1	100	480
Z1CBB002	7	100	480	100	15	3	J, T, CC	1	100	480
Z1CBB003	7	100	480	100	15	6	J, T, CC	1	100	480
Z1CBB004	7	100	480	100	15	6	J, T, CC	1	100	480
Z1CBB007	7	100	480	100	20	10	J, T, CC	1	100	480
Z1CBB011	7	100	480	100	25	15	J, T, CC	1	100	480
Z1CBB014	7	100	480	100	35	20	J, T, CC	1	100	480
Z1CBB021	7	100	480	100	50	35	J, T	1	100	480
Z1CBB027	7	100	480	100	60	45	J, T	1	100	480
Z1CBB034	7	100	480	100	80	50	J, T	1	100	480
Z1CBB040	7	100	480	100	100	70	J, T	1	100	480
Z1CBB052	7	100	480	100	125	90	J, T	1	100	480
Z1CBB065	7	100	480	100	150	110	J, T	1	100	480
Z1CBB077	7	100	480	100	175	125	J, T	1	100	480
Z1CBB096	7	100	480	100	225	150	J, T	1	100	480
Z1CBB124	7	100	480	100	300	200	J, T	1	100	480
Z1CBB156	7	100	480	100	350	250	J, T	1	100	480
Z1CBB180	7	100	480	100	450	300	J, T	1	100	480
Z1CBB240	7	100	480	100	600	400	J, T	1	100	480
Z1CBB302	7	100	480	100	700	500	J, T	1	100	480
Z1CBB361	7	100	480	100	800	600	J, T	1	100	480
Z1CBB414	7	100	480	100	1000	600	J, T	1	100	480
Z1CBB477	7	100	480	100	1000	800	L	1	100	480
Z1CBB515	7	100	480	100	1200	800	L	1	100	480
Z1CBB590	7	100	480	100	1200	1000	L	1	100	480
Z1CBD002	7	100	208	100	15	3	J, T, CC	1	100	208
Z1CBD003	7	100	208	100	15	6	J, T, CC	1	100	208
Z1CBD004	7	100	208	100	15	6	J, T, CC	1	100	208
Z1CBD006	7	100	208	100	15	10	J, T, CC	1	100	208
Z1CBD007	7	100	208	100	15	10	J, T, CC	1	100	208
Z1CBD010	7	100	208	100	25	15	J, T, CC	1	100	208
Z1CBD016	7	100	208	100	40	25	J, T, CC	1	100	208
Z1CBD024	7	100	208	100	60	40	J, T	1	100	208
Z1CBD030	7	100	208	100	70	50	J, T	1	100	208
Z1CBD046	7	100	208	100	110	80	J, T	1	100	208
Z1CBD059	7	100	208	100	150	100	J, T	1	100	208
Z1CBD074	7	100	208	100	175	125	J, T	1	100	208
Z1CBD088	7	100	208	100	200	150	J, T	1	100	208
Z1CBD114	7	100	208	100	250	175	J, T	1	100	208
Z1CBD143	7	100	208	100	350	250	J, T	1	100	208
Z1CBD169	7	100	208	100	400	250	J, T	1	100	208
Z1CBD211	7	100	208	100	500	350	J, T	1	100	208
Z1CBD273	7	100	208	100	600	450	J, T	1	100	208
Z1CBD343	7	100	208	100	800	600	J, T	1	100	208
Z1CBD396	7	100	208	100	800	600	J, T	1	100	208


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	<b>DRAWN BY:</b> K. MALUSIC	<b>DATE:</b> 5/15/12	<b>TITLE:</b> AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	<b>CHECKED:</b> K. FLIERL	<b>DATE:</b> 5/15/12			
	<b>TECH:</b>	<b>DATE:</b>			
	<b>APPROVED:</b> J. ZUEHLKE	<b>DATE:</b> 5/15/12	<b>SIZE:</b> C	<b>REVISION:</b> 03	<b>PAGE:</b> 7 of 9
	<b>ORIGINAL DESIGN:</b> K. FLIERL	<b>DATE:</b> 11/1/11	<b>DRAWING #:</b> UDA00727		

TABLE 7			
WORK ORDER PART NO. BEGINNING	WITH OPTION PC		
	USE FORMAT UNPN0081-SCCR_	①	②
Z1CBB001	1	65	480
Z1CBB002	1	65	480
Z1CBB003	1	65	480
Z1CBB004	1	65	480
Z1CBB007	1	65	480
Z1CBB011	1	65	480
Z1CBB014	1	65	480
Z1CBB021	1	65	480
Z1CBB027	1	65	480
Z1CBB034	1	65	480
Z1CBB040	1	65	480
Z1CBB052	1	65	480
Z1CBB065	1	65	480
Z1CBB077	1	65	480
Z1CBB096	1	65	480
Z1CBB124	1	65	480
Z1CBB156	1	65	480
Z1CBB180	1	65	480
Z1CBB240	1	65	480
Z1CBB302	1	65	480
Z1CBB361	1	65	480
Z1CBB414	1	65	480
Z1CBB477	1	65	480
Z1CBB515	1	65	480
Z1CBB590	1	65	480
Z1CBD002	1	65	208
Z1CBD003	1	65	208
Z1CBD004	1	65	208
Z1CBD006	1	65	208
Z1CBD007	1	65	208
Z1CBD010	1	65	208
Z1CBD016	1	65	208
Z1CBD024	1	65	208
Z1CBD030	1	65	208
Z1CBD046	1	65	208
Z1CBD059	1	65	208
Z1CBD074	1	65	208
Z1CBD088	1	65	208
Z1CBD114	1	65	208
Z1CBD143	1	65	208
Z1CBD169	1	65	208
Z1CBD211	1	65	208
Z1CBD273	1	65	208
Z1CBD343	1	65	208
Z1CBD396	1	65	208

TABLE 8			
WORK ORDER PART NO. BEGINNING	WITH OPTION PM		
	USE FORMAT UNPN0081-SCCR_	①	②
Z1CBB001	1	100	480
Z1CBB002	1	100	480
Z1CBB003	1	100	480
Z1CBB004	1	100	480
Z1CBB007	1	100	480
Z1CBB011	1	100	480
Z1CBB014	1	100	480
Z1CBB021	1	100	480
Z1CBB027	1	100	480
Z1CBB034	1	100	480
Z1CBB040	1	100	480
Z1CBB052	1	100	480
Z1CBB065	1	100	480
Z1CBB077	1	100	480
Z1CBB096	1	100	480
Z1CBB124	1	100	480
Z1CBB156	1	100	480
Z1CBB180	1	100	480
Z1CBB240	1	100	480
Z1CBB302	1	100	480
Z1CBB361	1	100	480
Z1CBB414	1	100	480
Z1CBB477	1	100	480
Z1CBB515	1	100	480
Z1CBB590	1	100	480
Z1CBD002	1	100	208
Z1CBD003	1	100	208
Z1CBD004	1	100	208
Z1CBD006	1	100	208
Z1CBD007	1	100	208
Z1CBD010	1	100	208
Z1CBD016	1	100	208
Z1CBD024	1	100	208
Z1CBD030	1	100	208
Z1CBD046	1	100	208
Z1CBD059	1	100	208
Z1CBD074	1	100	208
Z1CBD088	1	100	208
Z1CBD114	1	100	208
Z1CBD143	1	100	208
Z1CBD169	1	100	208
Z1CBD211	1	100	208
Z1CBD273	1	100	208
Z1CBD343	1	100	208
Z1CBD396	1	100	208



 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	<b>DRAWN BY:</b> K. MALUSIC	<b>DATE:</b> 5/15/12	<b>TITLE:</b> AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	<b>CHECKED:</b> K. FLIERL	<b>DATE:</b> 5/15/12			
	<b>TECH:</b>	<b>DATE:</b>			
	<b>APPROVED:</b> J. ZUEHLKE	<b>DATE:</b> 5/15/12	<b>SIZE:</b> C	<b>REVISION:</b> 03	<b>PAGE:</b> 8 of 9
<b>ORIGINAL DESIGN:</b> K. FLIERL	<b>DATE:</b> 11/1/11	<b>DRAWING #:</b> UDA00727			



TABLE 9			
WORK ORDER PART NO. BEGINNING	USE FORMAT UNPN0081-SCCR_	①	②
Z1B3B001	1	100	480
Z1B3B002	1	100	480
Z1B3B003	1	100	480
Z1B3B004	1	100	480
Z1B3B007	1	100	480
Z1B3B011	1	100	480
Z1B3B014	1	100	480
Z1B3B021	1	100	480
Z1B3B027	1	100	480
Z1B3B034	1	100	480
Z1B3B040	1	100	480
Z1B3B052	1	100	480
Z1B3B065	1	100	480
Z1B3B077	1	100	480
Z1B3B096	1	100	480
Z1B3B124	1	100	480
Z1B3B156	1	100	480
Z1B3B180	1	100	480
Z1B3B240	1	100	480
Z1B3B302	1	100	480
Z1B3B361	1	100	480
Z1B3B414	1	100	480
Z1B3B477	1	100	480
Z1B3B515	1	100	480
Z1B3B590	1	100	480
Z1B3D002	1	100	208
Z1B3D003	1	100	208
Z1B3D004	1	100	208
Z1B3D006	1	100	208
Z1B3D007	1	100	208
Z1B3D010	1	100	208
Z1B3D016	1	100	208
Z1B3D024	1	100	208
Z1B3D030	1	100	208
Z1B3D046	1	100	208
Z1B3D059	1	100	208
Z1B3D074	1	100	208
Z1B3D088	1	100	208
Z1B3D114	1	100	208
Z1B3D143	1	100	208
Z1B3D169	1	100	208
Z1B3D211	1	100	208
Z1B3D273	1	100	208
Z1B3D343	1	100	208
Z1B3D396	1	100	208

 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	<b>DRAWN BY:</b> K. MALUSIC	<b>DATE:</b> 5/15/12	<b>TITLE:</b> AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR Z1000		
	<b>CHECKED:</b> K. FLIERL	<b>DATE:</b> 5/15/12			
	<b>TECH:</b>	<b>DATE:</b>			
	<b>APPROVED:</b> J. ZUEHLKE	<b>DATE:</b> 5/15/12	<b>SIZE:</b> C	<b>REVISION:</b> 03	<b>PAGE:</b> 9 of 9
<b>ORIGINAL DESIGN:</b> K. FLIERL	<b>DATE:</b> 11/1/11	<b>DRAWING #:</b> UDA00727			